



## ATTRACTIVE DESIGN

The new attractive surround now fits dado backboxes as well as ordinary ones. Plus it allows more space for the cables behind the faceplate.

## BACKBOXES FOR FLUSH AND SURFACE MOUNT

Fully redesigned backboxes are easier to fit than ever and don't shatter. Also available as a spare is the new double-gang mud-ring which allows the Techconnect to be flush-mounted.

## UPGRADEABLE MODULAR FAMILY

Order as individual parts or convenient packages. The Techconnect is the only family of products which seamlessly integrates connectivity, audio, and projector control in one modular format.

## HIGH QUALITY CABLES

Installation-grade VGA cables all feature 'Display Data Channel' cores for true plug-and-play. All Vision cable has high quality copper and features properly distributed shielding.

## RoHS COMPLIANT

EU legislation dictates that lead-free solder must be used when soldering. The Techconnect is a solderless system meaning you can get on with the job.

## PRE-PREPARED

All cables have a moulded connector at one end to fix to the projector to avoid soldering at the top of ladders and the other end is stripped ready for fixing to the Techconnect connectors. This makes cable routing through tight spots easy. Cables can easily be cut down to length.

## QUICK AND EASY

Modules have 'Phoenix' screw termination for reliability and to avoid dry joint connections. No soldering proficiency is required.

## CLIP-IN MODULES

Featuring robust clip-in modules, built for tough environments. Fast fitting.




## Standard Package

for comprehensive installations



## Lite Package

for basic installations, allowing spare space for other modules including the amplifier or control module



SPECIFICATIONS	Standard Module Package	Standard 10m and 15m Cable Package	Lite Module Package	Lite 10m and 15m Cable Package
BOX DIMENSIONS	250 x 250 x 66mm	250 x 250 x 120mm	250 x 250 x 66mm	250 x 250 x 120mm
FACEPLATE DIMENSIONS	146 x 86 x 46mm	146 x 86 x 46mm	146 x 86 x 46mm	146 x 86 x 46mm
PACKAGED WEIGHT	0.5kg	10m: 3.0kg / 15m: 4.3kg	0.5kg	10m: 2.5kg / 15m: 3.8kg
COLOUR	White (RAL9010)	White (RAL9010)	White (RAL9010)	White (RAL9010)
INCLUDED	<ul style="list-style-type: none"> <li>2 x VGA/MiniJack</li> <li>1 x USB</li> <li>1 x 3-Phono</li> <li>1 x S-Video/2-Phono</li> <li>1 x RJ45</li> <li>1 x 4-Barewire speaker</li> <li>3 x Blanking panels</li> </ul>	<ul style="list-style-type: none"> <li>2 x VGA</li> <li>1 x S-Video</li> <li>1 x 1-Phono</li> <li>1 x 2-Phono</li> <li>1 x 15m MiniJack</li> </ul>	<ul style="list-style-type: none"> <li>1 x VGA/MiniJack</li> <li>1 x USB</li> <li>1 x 1-phono</li> <li>1 x 3-phono</li> <li>2 x Blanking panels</li> </ul>	<ul style="list-style-type: none"> <li>1 x VGA</li> <li>1 x 1-phono</li> <li>1 x 2-phono</li> <li>1 x 3.5mm minijack</li> </ul>
PALLET QUANTITY	384	208	384	224
WARRANTY	2-year return to base	2-year return to base	2-year return to base	2-year return to base
COMPLIANCES	RoHS, WEEE & CE compliant	RoHS, WEEE & CE compliant	RoHS, WEEE & CE compliant	RoHS, WEEE & CE compliant
ORDER PART	TC 1643907	TC2 5MCABLES 1740256 TC2 10MCABLES 1474525 TC2 15MCABLES 1474526	TC2-LT 1643286	TC2-LT5MCABLES 1740257 TC2-LT10MCABLES 1643287 TC2-LT15MCABLES 1643288
BUNDLE PARTS		TC2+TC2 5MCABLES 1783082 TC2+TC2 10MCABLES 1693872 TC2+TC2 15MCABLES 1693873		TC2-LT+TC2-LT5MCABLES 1740257 TC2-LT+TC2-LT10MCABLES 1688515 TC2-LT+TC2-LT15MCABLES 1688516

**SPARES** All parts shown above are available individually and all cables are available individually in 10, 15 and 20m lengths. In addition, the modules shown below are also available.

