

Sonos

The latest sound in fire alarm technology

Fitted with the **TimeSaver Base®**, the Sonos is a unique multi-purpose alarm sounder optimised for fire applications.

Installer Benefits

Unique

Wire-to-base system uses the TimeSaver® design.

Quick & Safe

Simple 'First Fix' installation (no 'Second Fix' wiring).
Smooth flow cabling for faster termination.

Twist & Click

Quick connect / disconnect.
No locking screw required.

Easy Handling

Tone and volume setting can be preset or adjusted 'off-base'.



Performance Benefits

Alarm Tones

32 distinct tones.

Efficiency

Current consumption from 6 to 35 mA.

Audibility

Up to 110 dB at peak.

Synchronisation

Automatic synchronisation.

Compliance

EN54 3:2001.

Integrated beacon

Improved all-round visibility due to large lens.



Sonos

A new standard in fire alarm sounders designed to fulfil requirements in a variety of applications.

Built in TimeSaver Base®


- Sounder locks into base. No wiring required to sounder head.
- Faster installation reduces commissioning time and overall costs.
- E-Z™ fit slots (for shallow base fixing).
- Timesaver system also on deep base option.

Weatherproof protection to IP65*


- Sonos can be used in all locations, both indoors and outdoors.

Combined sounder/beacon

- The full sounder head becomes a lens, thus providing greater spread of light.



TimeSaver® Shallow Base



Deep Base

*Applies to deep base option
TimeSaver Base® is a registered trademark of Apollo Fire Detectors.
E-Z™ Fit is a trademark of Apollo Fire Detectors

Colours:	Available in red and white	Operation:	Continuous and synchronised
Audibility:	110dBA @ 1 metre (tone dependent)	Frequency:	400-2850HZ
Tones:	32	Operating Temp:	-25°C to 70°C
Voltage:	8-35V DC, 110-230V AC	Construction:	Flame retardant polycarbonate
Current:	6-35 mA (tone dependent)	Cable entries:	2 glanded in deep base
IP Rating:	IP65*	Weight:	Sonos deep base 250g, Sonos shallow base 215g
Compliance:	EN54 3.2001 and BS5839 pt 1	Dimensions:	Sonos deep base: width 97.5mm, height 104.1mm Sonos shallow base: width 100mm, height 81.3mm

Sounder		Beacon		Sounder beacon	
8-35V dc:	Red shallow base 18-980450	0.7J/24V:	Red/red shallow base 18-980473	24V dc:	Red/red shallow base 18-980452
	White shallow base 18-980475		Red/amber shallow base 18-980479		Red/amber shallow base 18-980477
	Red deep base 18-980451		Red/red deep base 18-980472		Red/red deep base 18-980453
	White deep base 18-980476		Red/Amber deep base 18-980471		Red/amber deep base 18-980478
110/230VAC:	Red shallow base 18-980485	110/230VAC:	Red/red shallow base 18-980487		
	White shallow base 18-980486		Red/amber shallow base 18-980488		
	Red deep base 18-980480		Red/red deep base 18-980482		
	White deep base 18-980481		Red/amber deep base 18-980483		

While we make every effort to ensure the accuracy of the information printed, we disclaim any warranty or representation expressed or implied about its accuracy, completeness or appropriateness for a particular purpose. You assume full responsibility for using the information and you understand that neither Klaxon nor any of its employees or agents are responsible or liable for any claim, loss or damage resulting from its use.