

NEW!

Datamet

Datamet Wall Cases


Modern aluminium enclosures designed for indoor applications. Provide total access to the electronics during installation on the wall. Stylish design with die-cast front bezel, top cover and 'L' shape rear panel. Front panels and internal mounting plates ordered separately.

Datamet Wandgehäuse


Moderne Aluminium-Gehäuse für Innenanwendungen. Elektronik während der Wandinstallation frei zugänglich. Elegantes Design mit Zink-Druckguss Frontrahmen, Haube und Rückplatte in L-Form. Front- und Montageplatten als Zubehör.

Boîtiers Muraux Datamet

Des boîtiers en aluminium modernes pour des applications dans l'intérieur. Accès à l'électronique sans barrière pendant l'installation au mur. Design élégant avec bandeaux frontales, partie supérieure et panneau arrière en forme L moulés sous pression. Panneaux frontales et plaques internes à commander séparément.



Standard colours
Standardfarben
Coloris standard



Supply

- ① Top cover
- ② Rear panel
- ③ Front bezel
- ④ M4 x 16 mm (x4)
- ⑤ M4 x 6 mm (x2)
- ⑥ M3 x 6 mm (x4)
- ⑦ *Front panel
- * Accessories


Lieferumfang

- Oberteil
- Rückplatte
- Frontrahmen
- M4 x 16 mm (x4)
- M4 x 6 mm (x2)
- M3 x 6 mm (x4)
- *Frontplatten
- * Zubehör

Fourniture

- Partie supérieure
- Plaque arrière
- Cadre frontal
- M4 x 16 mm (x4)
- M4 x 6 mm (x2)
- M3 x 6 mm (x4)
- *Plaque avant
- * Accessoires


Datamet



Part No.	Version	W	H	D	A	B
Bestell-Nr./Réf.						
M 58 25 105	S	250 (9.842")	180 (7.086")	116 (4.567")	220.7 (8.689")	160.8 (6.330")
M 58 35 105	M	350 (13.779")	250 (9.842")	116 (4.567")	320.7 (12.625")	230.8 (9.086")
M 58 40 105	L	450 (17.716")	300 (11.811")	116 (4.567")	420.7 (16.563")	280.8 (11.055")

Front Panel


Frontplatten
Plaque Avant



Part No.	Version	A	B
Bestell-Nr./Réf.			
M 58 00 025	S	220 (8.661")	159.5 (6.280")
M 58 00 035	M	320 (12.598")	229.5 (9.035")
M 58 00 040	L	370 (14.567")	279.5 (11.004")

Mounting Plate Kit

Montageplatten-Set
Kit De Plaque Support



Supply: Mounting plate + ① x 6 + ② x 12
Lieferumfang: Montageplatten + ① x 6 + ② x 12
Fourniture: Plaque support + ① x 6 + ② x 12

Part No.	Version	A	B	C	D
Bestell-Nr./Réf.					
M 58 04 125	S	175 (6.890")	120 (4.724")		
M 58 04 135	M	275 (10.827")	190 (7.480")		
M 58 04 140	L	325 (12.795")	240 (9.449")		

Datamet



S




M



L

Front Panel



Mounting Plate Kit



FIRST ANGLE PROJECTION


Modifications

Iss

1

Detail "A"

4 off holes 4.0mm (0.157") dia



Tolerances unless otherwise stated:			
General tolerances ±0.20			
Resultant tolerances between hole centers ±0.15			
Tolerances on hole diameters ±0.05			
Angles ± 0.5°			
Surface finish 32/			
Required Finish		Scale	1:1
Etch &		Drawn by:	Ian Cox
Clear Anodise		Checked By:	
		Drawing Number	14,49
		Date drawn:	January '07
		Material Spec	2.0mm aluminium
ALL DIMENSIONS IN MILLIMETRES (Inches in brackets)			
DO NOT SCALE			
			
METCASE ENCLOSURES			
15 Brunel Way			
Segensworth East, Fareham,			
Hampshire, PO15 5TX, UK.			
www.metcase.com			
Part Name		Part Number	
Datamet Front Panel S		M5800025	
		Sheet 1 of 1	
©OKW ENCLOSURES LTD (DATE AS SHOWN) THIS DRAWING CONTAINS PROPRIETARY INFORMATION OF OKW ENCLOSURES LTD AND IS TENDERED SUBJECT TO THE FOLLOWING CONDITIONS: THE INFORMATION BE RETAINED IN CONFIDENCE, NOT BE REPRODUCED OR COPIED, AND NOT BE USED OR INCORPORATED IN ANY PRODUCT, UNLESS PERMISSION IS OBTAINED IN WRITING FROM OKW ENCLOSURES LTD			
A1			

©OKW ENCLOSURES LTD (DATE AS SHOWN). THIS DRAWING CONTAINS PROPRIETARY INFORMATION OF OKW ENCLOSURES LTD AND IS TENDERED SUBJECT TO THE FOLLOWING CONDITIONS: THE INFORMATION BE RETAINED IN CONFIDENCE, NOT BE REPRODUCED OR COPIED, AND NOT BE USED OR INCORPORATED IN ANY PRODUCT, UNLESS PERMISSION IS OBTAINED IN WRITING FROM OKW ENCLOSURES LTD.