

## THE DECK & OUTDOOR SCREW GOOD ENOUGH TO CARRY THE TDA'S DECKMARK™ ACCREDITATION



### Cross Recess (PZ2)

Industry standard - No searching for a driver bit.

### Part Thread

Eliminates 'jacking' where a full threaded screw tends to pull apart the jointed material.

### Single Thread

Drives in the wood without reaming, enabling a swift, efficient fix with high pull out retention.

### CPT™ Hardened

Permeated case with through hardening allows the perfect balance between core ductility and surface toughness - with the strength of a high tensile bolt the screw will not snap - no pilot hole required.

### Spiral Point

Immediate start.

### Installation

- Use a quality PZ2 drive bit & install the screw perpendicular to the deck.
- By increasing drill speed as the screw threads into the deck will reduce wood split.
- No pilot hole required in most applications.
- Drive the screw flush, do not overdrive.
- If cam-out occurs, remove and replace. (To eliminate cam-out use an impact driver).
- Use two screws at every joist as shown.


**Deck-Tite®'s unique 'thread pitch to Core Size Ratio' gives the perfect balance between ease of insertion and pull-out retention whilst increasing the core shear strength. It's Tri-Lock™ thread forms, not cuts, a thread in the material expanding the wood which then relaxes back around the screw ensuring a tight and locked fix. Once driven in the screw will not move, it is secure for good - no stubbed toes!**

Core Size Ratio means that only a 4.5mm gauge is necessary. Deck-Tite's threadform enables it to perform to the strength of a 4.8mm (10g) screw but poses the versatility of a slimmer screw.



### Collar

Gives strength to the most vulnerable point of the screw, whilst also allowing a deeper recess and less cam-out for a secure drive.



### Tri-Lock™ Threadform

Three flats on the thread means that as the screw is driven in there is less surface contact between the screw and timber, allowing less battery wear, easier insertion and the screw will not work loose as the boards are walked upon.


### Net-Coat™ Green for Outdoor use

Developed for the new pressure treated timber and outdoor use.

### Sizes

Metric	Imperial
4x25	(8x1)
4x40	(8x1.1/2)
4.5x50	(8x2)
4.5x57	(8x2.1/4)
4.5x63	(8x2.1/2)
4.5x75	(8x3)

Boxed in 200's



### THE ULTIMATE DECK & OUTDOOR SCREW.






## THE BRAND NAME FOR DECK SCREWS

Where Quality Does Actually Matter

With today's ever improving treatments developed to sustain the life of timber, you'd have thought fixings would have followed suit?



**WRONG!**

Almost-

Independent tests show that show that Net-Coat™ Green used on Deck-Tite®, enhanced in line with those developments in pressure treated timber, outlasts other inferior outdoor fixings in corrosion tests.



With so much money being invested in quality timber products you don't want to spoil all your hard work using inferior screws which will let you down....and your reputation!



We are proud that the Timber Decking Association recognises the advances we have made by awarding Deck-Tite Plus with the highly vaunted DeckMark™ accreditation.



For FREE samples or more information  
please call 0870 043 4571

