

**Enclosure
KLIPPON K41 RAL7001****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-2083

www.weidmueller.com



For many years, the name Klippon has stood for competence and quality in enclosures and customer-specific, connection-ready applications. Customer satisfaction is our number one priority. That is why we have updated and modernized our line of aluminium housings. These are improved products for all application requirements.

General ordering data

Order No.	9529200000
Part designation	KLIPPON K41 RAL7001
Version	Enclosures, 120 mm, 81 mm, 122 mm, Aluminium AlSi12
GTIN (EAN)	4008190918095
Qty.	1 pc(s).

**Enclosure
KLIPPON K41 RAL7001**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-2083
www.weidmueller.com

Technical data

Dimensions (1)

Weight	840 g	Length	81 mm
Width	122 mm	Height	120 mm
Fixing dimension, width	106 mm		

General information

Fixing dimension, width	106 mm	Material	Aluminium AISi12
Surface	textured	Colour code	RAL 7001
Cover fixing	M4 torx stainless steel screws with slot	Enclosure fixing	Holes 4 mm
Integral fixing	threaded holes M6	Material	Aluminium AISi12
Resistance to shocks	10.00 J	Sealing material	Silicone
Surface	textured		

Cable glands top/bottom

M 12	6	M 16	6
M20	3	M25	2
M32	1	Side of enclosure	left right

cable glands, left

M 12 (3)	4	M 20 (3)	2
----------	---	----------	---

cable glands, right

M 12 (2)	4	M 16 (2)	4
M 20 (2)	2	M 25 (2)	1
M 32 (2)	1	Side of enclosure	left right

horizontal assembly

WDU 10 / ZDU 10	1x6	WDU 2,5 / ZDU 2,5 / IDU 2,5	1x13
WDU 4 / ZDU 4	1x11	WDU 6 / ZDU 6	1x8

vertical assembly

WDU 2,5 / ZDU 2,5 / IDU 2,5 (2)	*		
---------------------------------	---	--	--

Approvals

Approvals institutes	CULUS; GOSTEX; MARITREG; GOSTME25
----------------------	--------------------------------------

Classifications

eClass 5.1	27-14-91-07	eClass 6.0	27-14-91-07
------------	-------------	------------	-------------