

**Enclosure
KLIPPON K71 RAL7001****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-2083

www.weidmueller.com



For many years, the name Klippon has stood for competence and quality in enclosures and customer-specific, connection-ready applications. Customer satisfaction is our number one priority. That is why we have updated and modernized our line of aluminium housings. These are improved products for all application requirements.

General ordering data

Order No.	9529270000
Part designation	KLIPPON K71 RAL7001
Version	Enclosures, 230 mm, 100 mm, 280 mm, Aluminium AlSi12
GTIN (EAN)	4008190919054
Qty.	1 pc(s).

Enclosure KLIPPON K71 RAL7001

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-2083
 www.weidmueller.com

Technical data

Dimensions (1)

Weight	2,925 g	Length	100 mm
Width	280 mm	Height	230 mm
Fixing dimension, width	260 mm		

General information

Fixing dimension, width	260 mm	Material	Aluminium AISi12
Surface	textured	Colour code	RAL 7001
Cover fixing	M4 torx stainless steel screws with slot	Enclosure fixing	Holes 4 mm
Integral fixing	threaded holes M6	Material	Aluminium AISi12
Resistance to shocks	10.00 J	Sealing material	Silicone
Surface	textured		

Cable glands top/bottom

M 12	42	M 16	30
M 40	4	M 50	3
M20	21	M25	12
M32	10	Side of enclosure	left right

cable glands, left

M 12 (3)	28	M 20 (3)	10
----------	----	----------	----

cable glands, right

M 12 (2)	28	M 16 (2)	18
M 20 (2)	10	M 25 (2)	8
M 32 (2)	3	M 40 (2)	2
M 50 (2)	2	Side of enclosure	left right

horizontal assembly

WDU 10 / ZDU 10	2x21	WDU 2,5 / ZDU 2,5 / IDU 2,5	2x42
WDU 4 / ZDU 4	2x35	WDU 6 / ZDU 6	2x26

Approvals

Approvals institutes	CULUS; GOSTEX; MARITREG; GOSTME25
----------------------	--------------------------------------

Classifications

eClass 5.1	27-14-91-07	eClass 6.0	27-14-91-07
------------	-------------	------------	-------------