


Label Index by Size



Part Number	Pieces Per Package	Material	Color	Labels Per Row	Label Width Inch (mm) A	Label Height Inch (mm) B	Horizontal Repeat Inch (mm) C	Top Margin Inch (mm) D	Left Margin Inch (mm) E	Labels Per Sheet
1.600" Label Width										
LAT-36-773-1	1,000	Metallized Polyester	Silver	4	1.600 (40.64)	0.375 (9.53)	1.920 (48.77)	0.875 (22.23)	0.620 (15.75)	100
1.875" Label Width										
LAT-10-652-10	10,000	Polyimide	Amber	4	1.875 (47.63)	0.250 (6.35)	2.000 (50.80)	0.875 (22.23)	0.314 (7.98)	156
LAT-10-747-10	10,000	Polyester	White	4	1.875 (47.63)	0.250 (6.35)	2.000 (50.80)	0.875 (22.23)	0.314 (7.98)	156
LAT-11-409-5	5,000	Polyolefin	White	4	1.875 (47.63)	0.375 (9.53)	2.000 (50.80)	0.875 (22.23)	0.310 (7.87)	100
LAT-11-747-5	5,000	Polyester	White	4	1.875 (47.63)	0.375 (9.53)	2.000 (50.80)	0.875 (22.23)	0.310 (7.87)	100
LAT-11-747-5-YL	5,000	Polyester	Yellow	4	1.875 (47.63)	0.375 (9.53)	2.000 (50.80)	0.875 (22.23)	0.310 (7.87)	100
LAT-13-409-2.5	2,500	Polyolefin	White	4	1.875 (47.63)	0.833 (21.16)	2.000 (50.80)	0.834 (21.18)	0.310 (7.87)	44
LAT-13-410-2.5	2,500	Polyolefin	White	4	1.875 (47.63)	0.833 (21.16)	2.000 (50.80)	0.834 (21.18)	0.310 (7.87)	44
LAT-13-707-2.5	2,500	Polyester	White	4	1.875 (47.63)	0.833 (21.16)	2.000 (50.80)	0.834 (21.18)	0.310 (7.87)	44
LAT-13-722-2.5	2,500	Polyester	Clear	4	1.875 (47.63)	0.833 (21.16)	2.000 (50.80)	0.834 (21.18)	0.310 (7.87)	44
LAT-13-747-2.5	2,500	Polyester	White	4	1.875 (47.63)	0.833 (21.16)	2.000 (50.80)	0.834 (21.18)	0.310 (7.87)	44
LAT-13-747-2.5-YL	2,500	Polyester	Yellow	4	1.875 (47.63)	0.833 (21.16)	2.000 (50.80)	0.834 (21.18)	0.310 (7.87)	44
LAT-13-759-2.5	2,500	Paper	White	4	1.875 (47.63)	0.833 (21.16)	2.000 (50.80)	0.834 (21.18)	0.310 (7.87)	44
LAT-13-712-2.5	2,500	Polyester	Clear	4	1.875 (47.63)	0.833 (21.16)	2.000 (50.80)	0.834 (21.18)	0.310 (7.87)	44
LAT-14-747-1.5	1,500	Polyester	White	4	1.875 (47.63)	1.330 (33.78)	2.000 (50.80)	0.834 (21.18)	0.315 (8.00)	28
2.000" Label Width										
LAT-31-707-1	1,000	Polyester	White	3	2.000 (50.80)	0.900 (22.86)	2.800 (71.12)	0.875 (22.23)	0.300 (7.62)	30
LAT-31-747-1	1,000	Polyester	White	3	2.000 (50.80)	0.900 (22.86)	2.800 (71.12)	0.875 (22.23)	0.300 (7.62)	30
LAT-31-759-1	1,000	Paper	White	3	2.000 (50.80)	0.900 (22.86)	2.800 (71.12)	0.875 (22.23)	0.300 (7.62)	30
LAT-33-707-1	1,000	Polyester	White	3	2.000 (50.80)	1.437 (36.50)	2.800 (71.12)	0.875 (22.23)	0.300 (7.62)	18
LAT-33-747-1	1,000	Polyester	White	3	2.000 (50.80)	1.437 (36.50)	2.800 (71.12)	0.875 (22.23)	0.300 (7.62)	18
LAT-33-759-1	1,000	Paper	White	3	2.000 (50.80)	1.437 (36.50)	2.800 (71.12)	0.875 (22.23)	0.300 (7.62)	18
2.500" Label Width										
LAT-21-707-1	1,000	Polyester	White	3	2.500 (63.50)	1.000 (25.40)	2.600 (66.04)	0.875 (22.23)	0.300 (7.62)	27
LAT-21-712-1	1,000	Polyester	Clear	3	2.500 (63.50)	1.000 (25.40)	2.600 (66.04)	0.875 (22.23)	0.300 (7.62)	27
LAT-21-747-1	1,000	Polyester	White	3	2.500 (63.50)	1.000 (25.40)	2.600 (66.04)	0.875 (22.23)	0.300 (7.62)	27
LAT-21-747-1-YL	1,000	Polyester	Yellow	3	2.500 (63.50)	1.000 (25.40)	2.600 (66.04)	0.875 (22.23)	0.300 (7.62)	27
LAT-21-773-1	1,000	Metallized Polyester	Silver	3	2.500 (63.50)	1.000 (25.40)	2.600 (66.04)	0.875 (22.23)	0.300 (7.62)	27
2.875" Label Width										
LAT-43-707-2.5	2,500	Polyester	White	20	2.875 (73.02)	0.375 (9.53)	—	0.875 (22.23)	1.450 (36.83)	40
3.000" Label Width										
LAT-12-652-2.5	2,500	Polyimide	Amber	2	3.000 (76.20)	0.375 (9.53)	3.200 (81.28)	0.875 (22.23)	1.150 (29.21)	50
LAT-12-709-2.5	2,500	Removable Polyester	White	2	3.000 (76.20)	0.375 (9.53)	3.200 (81.28)	0.875 (22.23)	1.150 (29.21)	50
LAT-12-747-2.5	2,500	Polyester	White	2	3.000 (76.20)	0.375 (9.53)	3.200 (81.28)	0.875 (22.23)	1.150 (29.21)	50
LAT-12-747-2.5-YL	2,500	Polyester	Yellow	2	3.000 (76.20)	0.375 (9.53)	3.200 (81.28)	0.875 (22.23)	1.150 (29.21)	50
LAT-32-747-1	1,000	Polyester	White	2	3.000 (76.20)	0.900 (22.86)	3.200 (81.28)	0.875 (22.23)	1.150 (29.21)	20
LAT-32-759-1	1,000	Paper	White	2	3.000 (76.20)	0.900 (22.86)	3.200 (81.28)	0.875 (22.23)	1.150 (29.21)	20
LAT-34-707-1	1,000	Polyester	White	2	3.000 (76.20)	1.437 (36.50)	3.200 (81.28)	0.875 (22.23)	1.150 (29.21)	12
LAT-34-747-1	1,000	Polyester	White	2	3.000 (76.20)	1.437 (36.50)	3.200 (81.28)	0.875 (22.23)	1.150 (29.21)	18
LAT-34-759-1	1,000	Paper	White	2	3.000 (76.20)	1.437 (36.50)	3.200 (81.28)	0.875 (22.23)	1.150 (29.21)	18
3.062" Label Width										
LAT-175-124 **	380	Paper	White/Colors	2	3.062 (77.77)	0.500 (12.70)	0.500 (12.70)	0.938 (23.83)	1.118 (30.18)	38
3.600" Label Width										
LAT-44-707-2.5	2,500	Polyester	White	2	3.600 (91.44)	0.375 (9.53)	—	0.875 (22.23)	0.650 (16.51)	40
6.625" Label Width										
LAT-178-759 **	165	Paper	White/Colors	1	6.625 (168.28)	0.625 (15.88)	—	0.875 (22.23)	0.938 (23.83)	15

Note: Labels in chart are sorted in order by width, height, 3 digit material number (within part number), then die number (within part number).

** Also available in: BL=blue, BR=brown, GR=green, GY=grey, OR=orange, PL=purple, RD=red, YL=yellow.
 To order a color, add a dash "-" after the material number, then add the color suffix.
 Standard product: Contact your Brady Identification Solutions distributor or Customer Service representative for ordering information.