


Category 5E RJ45 to RJ45 Shielded Low Smoke Zero Halogen Patch Cables


Designed for environments where PVC's combustive toxicity is restricted, L-com's shielded Low Smoke Zero Halogen (LSZH) Ethernet cables provide the ideal alternative. Featuring all-metal-body RJ45 connectors and aluminized polyester shielded cable with drain wire, these assemblies are designed to protect from EMI/RFI while maintaining high performance data transmission characteristics. Ensure the protection of your investment by utilizing these L-com exclusive LSZH cables. Ask about custom lengths and quantity pricing. Talk to us about your project today!

Category 5E Patch Cords

EIA568



Twisted Pair Pinning: 1 & 2, 3 & 6, 4 & 5, 7 & 8.

Category 5E Stranded
4 Pair Cable


Item #	Description	Color	1-9	10-24	25-99	100-249	250-499
RoHS Category 5E Shielded Low Smoke Zero Halogen Patch Cables							
This series features 26AWG stranded conductors and a 100% foil shield. The LSZH jacket is perfect for environments where PVC's combustive toxicity is restricted.							
TRD855SZ-1	Shielded Cat. 5E LSZH Cable, RJ45 / RJ45, 1.0 ft	Black	16.95	16.61	15.93	14.92	12.71
TRD855SZ-2	Shielded Cat. 5E LSZH Cable, RJ45 / RJ45, 2.0 ft	Black	17.45	17.10	16.40	15.36	13.09
TRD855SZ-3	Shielded Cat. 5E LSZH Cable, RJ45 / RJ45, 3.0 ft	Black	18.45	18.08	17.34	16.24	13.84
TRD855SZ-5	Shielded Cat. 5E LSZH Cable, RJ45 / RJ45, 5.0 ft	Black	19.95	19.55	18.75	17.56	14.96
TRD855SZ-7	Shielded Cat. 5E LSZH Cable, RJ45 / RJ45, 7.0 ft	Black	21.45	21.02	20.16	18.88	16.09
TRD855SZ-10	Shielded Cat. 5E LSZH Cable, RJ45 / RJ45, 10.0 ft	Black	23.45	22.98	22.04	20.64	17.59
TRD855SZ-15	Shielded Cat. 5E LSZH Cable, RJ45 / RJ45, 15.0 ft	Black	27.45	26.90	25.80	24.16	20.59
TRD855SZ-25	Shielded Cat. 5E LSZH Cable, RJ45 / RJ45, 25.0 ft	Black	34.95	34.25	32.85	30.76	26.21
TRD855SZ-50	Shielded Cat. 5E LSZH Cable, RJ45 / RJ45, 50.0 ft	Black	53.45	52.38	50.24	47.04	40.09
TRD855SZ-75	Shielded Cat. 5E LSZH Cable, RJ45 / RJ45, 75.0 ft	Black	72.45	71.00	68.10	63.76	54.34
TRD855SZ-100	Shielded Cat. 5E LSZH Cable, RJ45 / RJ45, 100.0 ft	Black	90.95	89.13	85.49	80.04	68.21
Twisted Pair Pinning: 1 & 2, 3 & 6, 4 & 5, 7 & 8.							

Category 5E Double Shielded Low Smoke Zero Halogen Patch Cables for High EMI/RFI Environments



When a single shield is not enough, L-com's exclusive double-shielded patch cables are ideal. EMI/RFI interference is drastically reduced due to L-com's superior cable shielding, a combination of a 100% foil plus a 60% braid shield. The Low Smoke Zero Halogen (LSZH) jacket allows this industrial patch cable to meet today's environmental and safety requirements.

Category 5E Patch Cords

EIA568



Twisted Pair Pinning: 1 & 2, 3 & 6, 4 & 5, 7 & 8.

Category 5E Stranded
4 Pair Cable

RoHS Category 5E Double Shielded LSZH 26AWG Stranded Patch Cables

This series features 26AWG stranded conductors that are flexible and easy to install even in tight spaces. L-com stocks lengths up to 300 ft and can ship most orders the same day.

TRD855DSZ-1	Double Shielded Cat. 5E LSZH Patch Cable, RJ45 / RJ45, 1.0 ft	Lt. Gray	22.99	21.15	19.31	17.47	15.63
TRD855DSZ-2	Double Shielded Cat. 5E LSZH Patch Cable, RJ45 / RJ45, 2.0 ft	Lt. Gray	23.99	22.07	20.15	18.23	16.31
TRD855DSZ-3	Double Shielded Cat. 5E LSZH Patch Cable, RJ45 / RJ45, 3.0 ft	Lt. Gray	24.99	22.99	20.99	18.99	16.99
TRD855DSZ-5	Double Shielded Cat. 5E LSZH Patch Cable, RJ45 / RJ45, 5.0 ft	Lt. Gray	26.99	24.83	22.67	20.51	18.35
TRD855DSZ-7	Double Shielded Cat. 5E LSZH Patch Cable, RJ45 / RJ45, 7.0 ft	Lt. Gray	28.99	26.67	24.35	22.03	19.71
TRD855DSZ-10	Double Shielded Cat. 5E LSZH Patch Cable, RJ45 / RJ45, 10.0 ft	Lt. Gray	31.99	29.43	26.87	24.31	21.75
TRD855DSZ-15	Double Shielded Cat. 5E LSZH Patch Cable, RJ45 / RJ45, 15.0 ft	Lt. Gray	36.99	34.03	31.07	28.11	25.15
TRD855DSZ-25	Double Shielded Cat. 5E LSZH Patch Cable, RJ45 / RJ45, 25.0 ft	Lt. Gray	46.99	43.23	39.47	35.71	31.95
TRD855DSZ-50	Double Shielded Cat. 5E LSZH Patch Cable, RJ45 / RJ45, 50.0 ft	Lt. Gray	71.99	66.23	60.47	54.71	48.95
TRD855DSZ-75	Double Shielded Cat. 5E LSZH Patch Cable, RJ45 / RJ45, 75.0 ft	Lt. Gray	96.99	89.23	81.47	73.71	65.95
TRD855DSZ-100	Double Shielded Cat. 5E LSZH Patch Cable, RJ45 / RJ45, 100.0 ft	Lt. Gray	121.99	112.23	102.47	92.71	82.95

L-com Exclusive



RoHS Category 5E Double Shielded LSZH 24AWG Solid Patch Cables

This series features 24AWG solid conductors allowing easy termination to IDC connectors. L-com stocks lengths up to 300 ft and can ship most orders the same day.

TRD855SIG-1	Double Shielded Cat. 5E LSZH Patch Cable, RJ45 / RJ45, 1.0 ft	Lt. Gray	17.45	17.10	16.40	15.36	13.09
TRD855SIG-2	Double Shielded Cat. 5E LSZH Patch Cable, RJ45 / RJ45, 2.0 ft	Lt. Gray	18.45	18.08	17.34	16.24	13.84
TRD855SIG-3	Double Shielded Cat. 5E LSZH Patch Cable, RJ45 / RJ45, 3.0 ft	Lt. Gray	19.45	19.06	18.28	17.12	14.59
TRD855SIG-5	Double Shielded Cat. 5E LSZH Patch Cable, RJ45 / RJ45, 5.0 ft	Lt. Gray	21.45	21.02	20.16	18.88	16.09
TRD855SIG-7	Double Shielded Cat. 5E LSZH Patch Cable, RJ45 / RJ45, 7.0 ft	Lt. Gray	23.45	22.98	22.04	20.64	17.59
TRD855SIG-10	Double Shielded Cat. 5E LSZH Patch Cable, RJ45 / RJ45, 10.0 ft	Lt. Gray	25.95	25.43	24.39	22.84	19.46
TRD855SIG-15	Double Shielded Cat. 5E LSZH Patch Cable, RJ45 / RJ45, 15.0 ft	Lt. Gray	30.95	30.33	29.09	27.24	23.21
TRD855SIG-25	Double Shielded Cat. 5E LSZH Patch Cable, RJ45 / RJ45, 25.0 ft	Lt. Gray	40.45	39.64	38.02	35.60	30.34
TRD855SIG-50	Double Shielded Cat. 5E LSZH Patch Cable, RJ45 / RJ45, 50.0 ft	Lt. Gray	63.95	62.67	60.11	56.28	47.96
TRD855SIG-75	Double Shielded Cat. 5E LSZH Patch Cable, RJ45 / RJ45, 75.0 ft	Lt. Gray	87.95	86.19	82.67	77.40	65.96
TRD855SIG-100	Double Shielded Cat. 5E LSZH Patch Cable, RJ45 / RJ45, 100.0 ft	Lt. Gray	111.45	109.22	104.76	98.08	83.59

Shop at **L-com.com** or call **1-800-343-1455**E-mail: sales@L-com.com Fax: 978-689-9484

"Great web site you have here -- All prices are clearly listed with bulk price, too. The descriptions and pictures are very helpful and detailed. Thanks." - Justin K.