

Serie 7400 Kraftform® pistol handle with Rapidaptor®, pre-set adjustable



Construction: With quick-release bitholder Rapidaptor® for insert and power bits
Pre-set torque: 3.0 Nm
Accuracy: ±6 % (EN ISO 6789)
Application: For 1/4" bits DIN 3126-C 6,3 and E 6,3
Handle: Kraftform®, pistol handle, multi-component

Code	Art.No.	Nm	Nm	mm	mm	mm	mm	mm	mm	mm
05074717001 ¹⁾	7462	1/4"	3,0	3,0-6,0	150	100	6"	4"	1	

¹⁾ Other pre-set values within the adjustable range can be delivered on request

7440/41/42 Kraftform® Torque screwdriver set 0,3 - 6 Nm



Code			
05074739001	7400	1 x 7440; 1 x 7441	1
	7400 Pistole	1 x 7442	
	840/1 Z Hex-Plus	1 x 2,0x25; 1 x 2,5x25; 1 x 3,0x25; 1 x 4,0x25; 1 x 5,0x25; 1 x 6,0x25	
	867/1 TZ TORX®	1 x TX 6x25; 1 x TX 7x25; 1 x TX 8x25; 1 x TX 9x25; 1 x TX 10x25; 1 x TX 15x25; 1 x TX 20x25; 1 x TX 25x25; 1 x TX 30x25	
	867/1 Z IP TORX PLUS®	1 x 6 IPx25; 1 x 7 IPx25; 1 x 8 IPx25; 1 x 9 IPx25; 1 x 10 IPx25; 1 x 15 IPx25; 1 x 20 IPx25; 1 x 25 IPx25; 1 x 30 IPx25	

7440/41 Kraftform® Torque screwdriver set 0,3 - 3 Nm



Code			
05074738001	7400	1 x 7440; 1 x 7441	1
	840/1 Z Hex-Plus	1 x 2,0x25; 1 x 2,5x25; 1 x 3,0x25; 1 x 4,0x25; 1 x 5,0x25; 1 x 6,0x25	
	867/1 TZ TORX®	1 x TX 6x25; 1 x TX 7x25; 1 x TX 8x25; 1 x TX 9x25; 1 x TX 10x25; 1 x TX 15x25; 1 x TX 20x25; 1 x TX 25x25; 1 x TX 30x25	
	867/1 Z IP TORX PLUS®	1 x 6 IPx25; 1 x 7 IPx25; 1 x 8 IPx25; 1 x 9 IPx25; 1 x 10 IPx25; 1 x 15 IPx25; 1 x 20 IPx25; 1 x 25 IPx25; 1 x 30 IPx25	

1550 PH Screwdriver for Phillips screws



Application: For Phillips screws
Blade: Round, mat nickel
Tip: DIN 5260-PH, ISO 8764-PH, Black Point
Handle: Kraftform Micro® with anti-roll protection and rotating cap; multi-component

Code		mm	mm	mm	mm	mm
05030110001	PH 00	60	97	2,5	2 3/8"	5
05030111001	PH 0	60	97	3,0	2 3/8"	5
05030112001	PH 1	80	97	4,0	3 1/8"	5

1555 PZ Kraftform Micro® Screwdriver for Pozidriv screws



Application: Suitable for Pozidriv®-screws
Blade: Round, mat nickel
Tip: DIN 5260-PZ, ISO 8764-PZ, Black Point
Handle: Kraftform Micro® with anti-roll protection and rotating cap, multi-component

Code		mm	mm	mm	mm	mm
05030115001	PZ 0	60	97	3,0	2 3/8"	5
05030116001	PZ 1	80	97	4,0	3 1/8"	5

¹⁾ Pozidriv = reg. trademark of European Industrial Service Ltd.