



Compact and handy high pressure washers for basic outdoor cleaning tasks

You can make good use of the C 110.3-5 X-tra pressure washer. It is handy sized and the built-in trolley makes it easy to transport.

This machine has a number of functions that cover basic cleaning needs and can be used for tasks around the house such as cleaning cars, motorcycles, small patios, paths and driveways.

PRODUCT FACTS

- CLICK & CLEAN (C&C) nozzle system ensures quick and easy change of nozzle.
- Reliable aluminium pump.
- Trolley for high mobility.
- Automatic start/stop.
- Compact and easy to store.
- Light weight makes it easy to transport.
- Easy to handle and operate.

Nilfisk

Nilfisk-ALTO UK
Gilwilly Industrial Estate Penrith, Cumbria CA 11 9BQ
Tel: +44 (0)1 768 86 89 95 - Fax: +44 (0)1 768 86 47 13

www.nilfisk-alto.co.uk

Prices subject to change without prior notice

United Kingdom

Print created: 04-11-2010 16:07
1 / 4

Model	C 110.3-5 X-TRA
Ref. no	126139568
Description	C110.3-5X-TRA UK




PRODUCT FEATURES


AUTOMATIC START/STOP	■
TROLLEY	■
CLICK & CLEAN (C&C) NOZZLE CONCEPT	■
ALUMINIUM PUMP	■
GUN WITH QUICK CONNECTION AND SWIVEL	■

INCL. ACCESSORIES

6411132 CLICK & CLEAN FOAM SPRAYE	■
126411158 COMPACT PATIO	
126481144 G2 GUN WITH INTERM.TUBE	■
126481145 G2 LANCE	■
126481137 HOSE 5M	■
126481123 POWERSPEED G2 LIGHT	■
126481114 TORNADO G2 Y	■

Technical specifications	C 110.3-5 X-TRA
CABLE LENGTH (M)	5
VOLTAGE (V)	230
MOTOR RATED POWER (KW)	1.4
POWER CONSUMPTION (A)	6.1
WATER FLOW QMAX/QIEC (L/H)	440 - 310
PUMP PRESSURE (BAR/MPA)	max. 110 / max. 11
HOSE LENGTH (M)	5
MAX INLET TEMPERATURE (°C)	40
DIMENSIONS LXWXH (MM)	240x240x660
WEIGHT (KG)	7

Accessories	Ref. no	Min. required	C 110.3-5 X-TRA
	Options		
NILFISK BA VALVE COMPLETE	106411177	1	■
	Consumer pressure washer acc.		
WATER FILTER	106411231	1	■
GARDEN BRUSH	106411325	1	■
RIM BRUSH	106411326	1	■
HEAD FOR GARDEN BRUSH	106411327	1	■
HEAD FOR RIM BRUSH	106411328	1	■
7M HP HOSE EXCELLENT	106411346	1	■
COMPACT PATIO	126411158	1	■
WATER SUCTION KIT	126411387	1	■
ROTARY BRUSH	126411395	1	■
POWERSPEED G2 LIGHT GREEN	126481123	1	■
HOSE 5M	126481137	1	■
G2 GUN WITH INTERM.TUBE	126481144	1	■
G2 LANCE	126481145	1	■
EXTENSION HOSE 7M	6410760	1	■
ROTARY BRUSH	6410762	1	■
UNDERCHASSIS WASH LANCE	6410763	1	■
AUTO BRUSH	6410765	1	■
DRAIN/TUBE CLEANER 15M	6410766	1	■
VSB 120-1 (GREEN)	6410891	1	■
EXTENSION HOSE DYNAMIC 7M	6411048	1	■
AUTO BRUSH WITH SQUEEGEE	6411131	1	■
AUTO KIT CLICK & CLEAN	6411134	1	■
UNDERCHASSIS NOZZLE	6411135	1	■
AUTO NOZZLE	6411136	1	■
MULTI ANGLE ADAPTOR	6411138	1	■
TORNADO G2 Y	126481114	1	■
PATIO CLEANER PLUS ACC	126411376	1	■
CLICK & CLEAN FOAM SPRAYE R	6411132	1	■
	Detergents		
CAR COMBI CLEANER BOX 4X2 .5LTR	308000095	1	■
METAL CLEANER BOX 4 X 2.5 LTR	308000096	1	■

Accessories	Ref. no	Min. required	C 110.3-5 X-TRA
Detergents			
 PLASTIC CLEANER BOX 4X 2.5 LTR	308000097	1	■
STONE & WOOD CLEANER BOX 4X2.5	308000098	1	■
WOOD CLEANER BOX 4 X 2.5L TR	308000099	1	■