

GLASSGUARD

RECYCLABLE

SHATTER RESISTANT SAFETY LAMPS

20,000 HOUR COATING LIFE
FOR STANDARD + TRI PHOSPHOR LAMPS

Coating will not discolour, flake, melt or drip

Coating guaranteed to outperform lamp life

Will operate in both open & enclosed IP65 rated fittings

Complies with IEC Lamp safety and performance specifications

Free Lamp recycling service

(Only applies to new generation GlassGuard™)



CONTACT NOW FOR DISCOUNTS

TELEPHONE: 01842 763752 • FAX 01842 765252

E: sales@fotolec.com • www.fotolec.com

5 BAIRD WAY • FISON WAY INDUSTRIAL ESTATE • THETFORD • NORFOLK IP24 1JA

**NEW
PRODUCT
LAUNCH**



RECYCLABLE

SHATTER RESISTANT SAFETY LAMPS

SPECIFICATION DATA

Material: F.E.P (No Toxic U.V Retardants)

F.D.A Approved: In Compliance With 21CFR 177.1550 Regulatory Status

Coating Life Guarantee: + 20,000 hours

Resistance to Heat & Fire: Passes IEC60695-2-1/0

Maximum Continuous Operating Temperature: 200°C

Working Ambient Temperatures: Passes IEC60081 -25°C to +50°C

Light Loss Through Coating: < 5%

CE Marking Compliance: Passes IEC61195 Fluorescent Lamp Safety Specifications

T8			STANDARD PRODUCT LIST			T12		
Stock Code	Description	Net Trade Price Each	Stock Code	Description	Net Trade Price Each	Stock Code	Description	Net Trade Price Each
1535/S	18" 15W 35 White	£4.18	2035/S	2ft 20W 35 White	£4.08			
1533/S	18" 15W 33 Cool White	£4.18	2033/S	2ft 20W 33 Cool White	£4.08			
1584/S	18" 15W 840 Cool White	£5.35						
1835/S	2ft 18W 35 White	£3.61	4035/S	4ft 40W 35 White	£5.88			
1833/S	2ft 18W 33 Cool White	£3.61	4033/S	4ft 40W 33 Cool White	£5.88			
1884/S	2ft 18W 840 Cool White	£5.35	658035/S	5ft 65-80W 35 White	£6.75			
3035/S	3ft 30W 35 White	£4.56	658033/S	5ft 65-80W 33 Cool White	£6.75			
3033/S	3ft 30W 33 Cool White	£4.56	758535/S	6ft 75-85W 35 White	£8.21			
3084/S	3ft 30W 840 Cool White	£6.15	758533/S	6ft 75-85W 33 Cool White	£8.21			
3635/S	4ft 36W 35 White	£5.06	10035/S	8ft 100W 35 White	£10.56			
3633/S	4ft 36W 33 Cool White	£5.06	10033/S	8ft 100W 33 Cool White	£10.56			
3684/S	4ft 36W 840 Cool White	£6.38	12535/S	8ft 125W 35 White	£10.56			
5835/S	5ft 58W 35 White	£5.94	12533/S	8ft 125W 33 Cool White	£10.56			
5833/S	5ft 58W 33 Cool White	£5.94						
5884/S	5ft 58W 840 Cool White	£7.15						
7035/S	6ft 70W 35 White	£7.00						
7033/S	6ft 70W 33 Cool White	£7.00						
7084/S	6ft 70W 840 Cool White	£9.20						

Other Special & Standard Colours Available
Please Contact Our Sales Office For Details

CONTACT NOW FOR DISCOUNTS

TELEPHONE: 01842 763752 • FAX 01842 765285

E: sales@fotolec.com • www.fotolec.com

5 BAIRD WAY • FISON WAY INDUSTRIAL ESTATE • THETFORD • NORFOLK IP24 1JA