

ESD PROFI-SET **TRENDY** 2280 AND 2285

The professional kid for ESD-Specialists for local and mobile use



2280 **BERNSTEIN** ESD Profi-Set **TRENDY**
with tool set including ESD handling set

2285 **BERNSTEIN** ESD Profi-Set **TRENDY**
with tool set

Description:

Selected ESD-tools in handy plastic case made from conductive material. The tools are clearly arranged in accurate-sized cutouts in conductive hardfoam. For individual accessories are one resp. two cutouts available.

Outside dimensions: 350 x 310 x 65 mm (when closed)

Tool set:



Weight : approx.1.650 / 1.500 kg

No.	Description of individual tools
2-620	PLCC extractor
3-133-13	Side cutters , 120 mm, with conductive black hand-guard
3-651-15	Mini side cutters EUROline-Conductive , 120 mm, without sideface, for soft wire up to 0.6 mm Ø, copper wire up to 1.2 mm Ø, box joint, double leaf spring, fine polished and bright burnished, conductive bicoloured hand-guard
3-682-15	Flat nose pliers EUROline-Conductive , 130 mm, as above
3-683-15	Snipe nose pliers EUROline-Conductive , 130 mm, short jaws, as above
4-601	Screwdriver 50 x 0.8 mm , with conductive handle, blade from chrome vanadium, chrome-plated, with black tip
4-603	Screwdriver 50 x 1.5 mm , with conductive handle, blade from chrome vanadium, chrome-plated, with black tip
4-605	Screwdriver 60 x 2.0 mm , with conductive handle, blade from chrome vanadium, chrome-plated, with black tip
4-621	Cross-recess screwdriver size 000 , with conductive handle, blade from chrome vanadium, chrome-plated, with black tip
4-622	Cross-recess screwdriver size 00 , with conductive handle, blade from chrome vanadium, chrome-plated, with black tip

No.	Description of individual tools
4-623	Cross-recess screwdriver size 0 , with conductive handle, blade from chrome vanadium, chrome-plated, with black tip
5-049-13	SMD-tweezers , 110 mm, straight, very sharply pointed, ESD-coating
5-055-13	SMD-tweezers , 120 mm, sickle-shaped, very sharply pointed, as above
5-059-13	SMD-tweezers , 120 mm, flat, rounded tips, 2.0 mm width, as above
6-661	TORX screwdriver T 5 , with conductive handle, blade made from chrome vanadium, chrome-plated, with black tip
6-662	TORX screwdriver T 6 , with conductive handle, blade made from chrome vanadium, chrome-plated, with black tip
6-663 L	TORX screwdriver T 7 , with bore-hole in the tip, with conductive handle, blade made from chrome vanadium, chrome-plated, with black tip
7-422	ESD brush , bristles width 20 mm
9-354	ESD handling set (only in set 2280), consisting of: foldable, green workbench pad (surface resistance according to DIN 53482: approx. 10 ⁸ ohm), 500 x 400 x 0.35 mm, contact bracelet with spiral cord, earth wire 2500 mm long with 1 Mohm safety resistor including crocodile clip