for all types of applications, designed for long wear; quality

co. uction equals that of high priced counterparts. Skin packed in pairs or bulk packed. Add suffix "B" when ordering in bulk. Handles designated with (*) are bulk packed only.



H-9170 Clear anodized aluminum. Mounting centers: 2³/₄". Hardware: (2) 8-32 x ⁵/₈" screws. Hand clearance 13/16".



H-9174 Clear anodized aluminum. Mounting centers: 4". Hardware: (2) 8-32 x 3/s" screws. Hand clearance 13/32".



H-9176 Clear anodized aluminum. Mounting centers: 31/4". Hardware: (2) 8-32 x 3/8" screws. Hand clearance 3/4".



H-9177 Clear anodized aluminum. Mounting centers: 4³/₆". Hardware: (2) 8-32 x ³/₆" screws. Hand clearance 3/4".



H-9179 Clear anodized aluminum. Mounting centers: 4". Hardware: (2) 8-32 x 3/8" screws. Hand clearance 5/8".



H-9180 Clear anodized aluminum. Black trim. Mounting centers: 4". Hardware: (2) 8-32 x 1/4" screws.



H-9183 Clear anodized aluminum. Mounting centers: 49/16". Hardware: (2) 8-32 x 3/8" screws. Minimum hand clearance 13/32".



H-9110 Chrome Plated. Mounting centers: 6". Hardware: (2) 10-32 x 3/6" screws. Hand clearance 11/4". Material: 3/6" dia. steel, angular formed.



H-9111 Chrome Plated. Mounting centers: 4". Hardware: (2) 10-32 x ³/s" screws. Hand clearance ¹⁵/16". Material: ³/s" dia. steel.





H-9112 Chrome Plated. Mounting centers: 6". Hardware: (2) 10-32 x 3/s" screws. Hand clearance 15/16".
Material: 3/s" dia. steel.

FLUSH LATCHES



Official Control	Width	FitsPenel
*H-9352	155/64"	13 ga.
*H-9350	17/84"	16 ga.





H-9113 Chrome Plated. Mounting centers: 8". Hardware: (2) 10-32 × 3/8" screws. Hand clearance 15/16". Material: 3/8" dia. steel.



H-9114 Chrome Plated. Mounting centers: 8". Hardware: (2) 1/4"-28 Hex nuts. Hand clearance 11/2". Material: 1/2" dia. steel.



*H-9115 Chrome Plated. Mounting centers: 4 Hardware: (2) 1/4"-28 Hex nuts. Hand clearance 15/16". Material: 3/8" dia. steel.



*H-9116 Chrome Plated. Mounting centers: 6". Hardware: (2) 1/4"-28 Hex nuts. Hand clearance 15/16". Material: 3/6" dia. steel.



*H-9160 Chrome Plated. Mounting centers: 31/2". Hardware: (2) 1/4"-28 Hex nuts. Hand clearance 111/16". Material: 3/8" dia. steel.



*H-9161 Chrome Plated. Mounting centers: 51/4". Hardware: (2) 1/4"-28 Hex nuts. Hand clearance 111/16". Material: 3/8" dia. steel.



*H-9162 Chrome Plated. Mounting centers: 7". Hardware: (2) 1/4"-28 Hex nuts. Hand clearance 111/16". Material: 3/8" dia. steel.



*H-9163 Chrome Plated. Mounting centers: 83/4". Hardware: (2) 1/4"-28 Hex nuts. Hand clearance 1 11/16". Material: 3/6" dia. steel.



*H-9164 Chrome Plated. Mounting centers: 10¹/₂". Hardware: (2) ¹/₄"-28 Hex nuts. Hand clearance 1 ¹¹/₁₆". Material: ³/₆" dia. steel.



*H-9165 Chrome Plated. Mounting centers: 121/4". Hardware: (2) 1/4"-28 Hex nuts. Hand clearance 1 11/16". Material: 3/8" dia. steel.



H-9166 Chrome Plated. Mounting centers: 1²⁹/₃₂". Hardware: (2) 6-32 x 1/₂" screws. Hand clearance 1". Material: 1/4" dia. brass.

H-9168 Chrome Plated. Mounting centers: 3". Hardware: (2) 6-32 x ½" screws. Hand clearance 1". Material: 1/4" dia. brass.



H-9149 Recessed Handle Brushed chrome handle fits flush into die cast receptacle. Handle is $2^{1/2}$ " x $4^{3/6}$ ". Hand clearance $1^{29/32}$ ". Standard on Bud Classic II cabinets. Sold in pairs.

NON-LOCKING LATCH HANDLE Interchangeable with existing

key lock. LH-9358 used on 60, All American and Economizer, Front and Rear Doors and 2000 Rear Doors.

