



UNCONTROLLED DOCUMENT

PART NUMBER
SSB-DL6028GC

REV.
E

REV.	E.C.N. NUMBER AND REVISION COMMENTS	DATE
A	CHG'D TABLE FOR INDIVIDUAL MODULES.	9-9-93
B	E.C.N. #10113. & #10146./	4-23-96
C	E.C.N. #10222./	8-1-96
D	E.C.N. #10BRDR. & REDRAWN.	9-25-98
E	E.C.N. #11148.	5.14.07



NOTES:

1. SSH-DL6028W.
2. SSB-LX02GC LED. (5 PCS.)
3. PAINT BOTTOM AND EDGES 1, 2, AND 3 HIGH REFLECTIVE WHITE.

⊠ ELECTRO-OPTICAL CHARACTERISTICS $T_A=25^\circ\text{C}$ $I_f=960\text{mA}$

PARAMETER	GREEN	UNITS
PEAK COLOR WAVELENGTH	565	nm
FORWARD VOLTAGE (TYP)	4.2	V_f
LIGHT OUTPUT (TYP)	45	cd/m^2
VIEWING ANGLE (TYP)	180	$2x$ theta
EMITTED COLOR:	GREEN	

LIMITS OF SAFE OPERATION AT 25°C PER LED

PARAMETER	MAX	UNITS
PEAK FORWARD CURRENT*	150	mA
STEADY CURRENT	25	mA
REVERSE VOLTAGE	8	mA
POWER DISSIPATION	125	mW
DERATE FROM 25°C	-1.2	$\text{mW}/^\circ\text{C}$
OPERATING TEMP.	-20 TO +70	$^\circ\text{C}$
STORAGE TEMP.	-40 TO +80	$^\circ\text{C}$
SOLDERING TEMP.	+240	$^\circ\text{C}$
2.0mm FROM BODY		3 SEC. MAX

* $t < 10\mu\text{s}$



UNCONTROLLED DOCUMENT

*UNLESS OTHERWISE SPECIFIED TOLERANCES PER DECIMAL PRECISION ARE: X=±1 (±0.039), XX=±0.5 (±0.020), XXX=±0.25 (±0.010), XXXX=±0.127 (±0.005). LEAD SIZE=±0.05 (±0.002), LEAD LENGTH=±0.75 (±0.030). MIN= +DECIMAL PRECISION -0.00 MAX.= +0.00 -DECIMAL PRECISION

REV. E	PART NUMBER SSB-DL6028GC
55mm x 29mm LCD, 5 MODULE BACKLIGHT, 565nm GREEN CLEAR LEDS.	

CONFIDENTIAL INFORMATION
THE INFORMATION CONTAINED IN THIS DOCUMENT IS THE PROPERTY OF LUMEX INC. EXCEPT AS SPECIFICALLY AUTHORIZED IN WRITING BY LUMEX INC., THE HOLDER OF THIS DOCUMENT SHALL KEEP ALL INFORMATION CONTAINED HEREIN CONFIDENTIAL AND SHALL PROTECT SAME IN WHOLE OR IN PART FROM DISCLOSURE AND DISSEMINATION TO ALL THIRD PARTIES.

RELIABILITY NOTE
OUR MANY YEARS OF EXPERIENCE DATA ACCUMULATION INDICATE THAT SOLDER HEAT IS A MAJOR CAUSE OF EARLY AND FUTURE FAILURE. PLEASE PAY ATTENTION TO YOUR SOLDERING PROCESS.

290 E. HELEN ROAD
PALATINE, IL 60067-6976
PHONE: +1.847.359.2790
US WEB: www.lumex.com
TW WEB: www.lumex.com.tw

DRAWN BY: jc	CHECKED BY:	APPROVED BY:	DATE: 8.12.93
			PAGE: 1 OF 1
			SCALE: N/A