

**Justrite #14027 with Permanently  
Static Dissipative Plastic**

**Static Dissipative:** Complies with MIL-B-81705B/C

**Surface Resistivity:**  $1 \times 10^8$  to  $10^{11}$  ohms/sq

**Volume Resistivity:**  $1 \times 10^8$  to  $10^{11}$  ohms/sq

**Static Decay:** 5KV to Technical 0

2.0 Sec. @ 40% RH

**Active Ingredient:** Laurelamide

**Triboelectric Charge:** None

in compliance with


ODD HDBK 263/

ODD-STD-1686A/

NFPA Code 56A



**When  
Contamination is  
Not an Option....**



**More Safety Solutions From Justrite**

When your procedures require safe and effective handling of hazardous materials including solvents and flammables, look for solutions from **Justrite**, a worldwide leader in modern workplace safety.



**SAFETY WITH EFFICIENCY**

454 Dempster St., Des Plaines, IL 60016 USA  
Phone 1-847-298-9250 Fax 1-847-298-3429

1997 Justrite Mfg. Co. LLC


Subsidiary of Federal Signal Corp.




Justrite 'One-Touch' Liquid Dispensers can prevent costly interruptions to work flow in all work environments where liquids must remain uncontaminated – including clean rooms, laboratories, electronics assembly, hospitals, medical facilities and anywhere production processes require small, controlled amounts of liquids.

## ... You Can Depend on Justrite


- Simplicity of Fingertip Control
- Ultra-Pure Contents
- Chemical Conservation
- OSHA Compliance  
29CFR 1910.106 (e)(2)(iv)(a)



**No cap to remove or lose**



Press down, liquid pumps up and won't drain back into container. The precision stainless steel pump seals all contents and minimizes evaporation loss while protecting against the escape of toxic and/or flammable vapors.



**FM Approved...**  
Dispenser #14023 has undergone thorough testing at Factory Mutual and is available whenever authorities having jurisdiction request third party certification.



Model	Capacity	Description	Dimensions	Packages
14022	4 oz. 118 ml	Chemical Dispenser	2" x 2" x 3.25" 51mm x 51mm x 83mm	12/cart
14026	6 oz. 177ml	Chemical Dispenser	2.25" x 2.25" x 4.25" 57mm x 57mm x 108mm	12/cart
14028	8 oz. 236ml	Chemical Dispenser	2.25" x 2.25" x 5" 57mm x 57mm x 127mm	12/cart
14023	4 oz. 118ml	FM Approved Chemical Dispenser	2" x 2" x 3.25" 51mm x 51mm x 83mm	12/cart
14027	6 oz. 177ml	Anti-Static Chemical Dispenser	2.25" x 2.25" x 4.25" 57mm x 57mm x 108mm	12/cart

### 5 Models – 3 Sizes

Justrite 'One-Touch' Dispensers feature HDPE reservoirs and stainless steel pumps with a lifetime guarantee to deliver the first time, every time. For convenience, a set of pressure sensitive contents identification labels is included with each dispenser. Dispensers are ideal for alcohols, acetone, MEK, liquid flux, D.I. water, ammonia, nitric acid (0-30%), hydrochloric acid, ethyl acetate and other liquids.