

Technical Specifications

Printing Method

Thermal Transfer Printhead (180dpi)

Physical Characteristics

Dimensions

Length: 70mm,
Width: 114mm
Height: 212mm
Weight: 519grams

Keyboard

ABC-layout

To access international characters: Rapid Accented Character Entry, according to the mobile phone principle.

LCD display

2 lines
Rechargeable battery pack life indicator
Display backlighting

Extra protective bumper

Cutter

Operating characteristics

Operating conditions: T°: 4°C-40°C
Humidity 10%-90% RH
Storage conditions: T°: 0°C-90°C
Humidity 10%-90% RH
CE approved

Handheld Part Descriptions

PRINTER & ACCESSORIES

Description	
T107M-SMS-PRINTER-KIT-UK ¹	- Printer Kit - UK adaptor included
T107M-SMS-PRINTER-KIT-EU ¹	- Printer Kit - European adaptor included
T107M-SMS-PRINTER-EU	- Printer only (European)
SMS-CARRY STRAP	- Soft carry strap
SMS-EU-A/C-ADAPTOR ²	- EU Power adaptor
SMS-ASIA-A/C-ADAPTOR ²	- UK & Asia A/C Power adaptor
SMS-BATTERY-PACK ³	- Rechargeable battery pack
SMS-PRINTER-HARDCASE ⁴	- Hard case



Printer Kit Contents - Printer, rubber protection bumper, user guide, 6AA batteries, power adaptor, hard carry case and two tape cassettes (19mm white flexible nylon tape & 12mm white permanent polyester tape).

CASSETTES⁵

Description	Material	Cable Diameter Range	Length	Shrink Ratio	Colour	Technical Datasheet
SMS-TMS-3.9-4	Heat shrink tubing	1.18mm - 2.33mm	1.5m	3:1	Yellow	TTDS-122
SMS-TMS-3.9-9	Heat shrink tubing	1.18mm - 2.33mm	1.5m	3:1	White	TTDS-122
SMS-TMS-5.2-4	Heat shrink tubing	1.73mm - 3.73mm	1.5m	3:1	Yellow	TTDS-122
SMS-TMS-5.2-9	Heat shrink tubing	1.73mm - 3.73mm	1.5m	3:1	White	TTDS-122
SMS-TMS-7.9-4	Heat shrink tubing	2.97mm - 5.13mm	1.5m	3:1	Yellow	TTDS-122
SMS-TMS-7.9-9	Heat shrink tubing	2.97mm - 5.13mm	1.5m	3:1	White	TTDS-122
SMS-TMS-13.2-4	Heat shrink tubing	4.64mm - 8.70mm	1.5m	3:1	Yellow	TTDS-122
SMS-TMS-13.2-9	Heat shrink tubing	4.64mm - 8.70mm	1.5m	3:1	White	TTDS-122

Description	Material	Width	Length	Colour	Technical Datasheet
SMS-NC-12-4	Nylon Cloth	12mm	3.5m	Yellow	TTDS-123
SMS-NC-12-9	Nylon Cloth	12mm	3.5m	White	TTDS-123
SMS-NC-19-9	Nylon Cloth	19mm	3.5m	White	TTDS-123
SMS-PPNA-6-9	Non adhesive tag	6mm	5.5m	White	TTDS-124
SMS-PPNA-9-9	Non adhesive tag	9mm	5.5m	White	TTDS-124
SMS-V-12-4	Coloured vinyl	12mm	5.5m	Yellow	TTDS-125
SMS-V-12-9	Coloured vinyl	12mm	5.5m	White	TTDS-125
SMS-V-19-2	Coloured vinyl	19mm	5.5m	Red	TTDS-125
SMS-V-19-4	Coloured vinyl	19mm	5.5m	Yellow	TTDS-125
SMS-V-19-5	Coloured vinyl	19mm	5.5m	Green	TTDS-125
SMS-V-19-9	Coloured vinyl	19mm	5.5m	White	TTDS-125
SMS-WP-12-9	Polyester	12mm	5.5m	White	TTDS-126
SMS-WP-19-9	Polyester	19mm	5.5m	White	TTDS-126
SMS-MP-12-8A	Polyester	12mm	5.5m	Metalized	TTDS-127
SMS-MP-19-8A	Polyester	19mm	5.5m	Metalized	TTDS-127

Tyco Electronics UK Ltd
Cheney Manor Industrial Estate
Swindon
Wiltshire SN2 2QE
Phone: +44 (0) 1793 572271

Tyco Electronics idento GmbH
Paul-Ehrlich-Strasse 23
D-63322 Roedermark
Phone: +49 (0) 60 74 89 08 0

Tyco Electronics France
29, chaussée Jules Cesar
BP 39
95301 Pontoise Cedex
Phone: +33 (0) 1 34 20 88 88

tyco
Electronics



Versatile high-performance
identification & labelling
made fast and easy


Versatile high-performance identification & labelling made fast and easy



The new T107M from Tyco Electronics is perfect for the professional user who needs an affordable label printer for on-site applications that's tough and easy to use. Contractors, panel builders and facility managers will save time and money by using the special Hot Keys that provide labels at the touch of a button including wire and cable wraps, module marking, fixed length, serialization, vertical printing, barcodes, symbols and much more.


The T107M offers clear, smudge-free high-performance labels that stick permanently to a variety of surfaces and provides remarkable MIL-spec print permanence on Heat Shrink Tubing. Print media is offered in easy-to-load cassettes and includes an optimized ribbon and choice of material: Heat Shrink & Nylon Cloth, Vinyl, Polyester and Polypropylene labels.

Wire & Cable/
Heatshrink



Hotkeys

Wrapping



Fixed Length



Vertical Printing



Module Marking



Patch Panel



Features and Benefits

- Affordable
- Easy to use
- Special 'Hot Key' functionality
- Extra large 30-character backlit display
- Oversized keys
- Bright orange in colour, ensuring it will not get lost
- Rubber bumper for extra protection
- Also available in kit form
- Easy to install cassettes