



# Technical Cleaning Brushes

2030-2033

## Introduction

---

Techspray® has designed a brush line which offers a brush for your specific needs, whether you are cleaning sensitive optics or scrubbing heavy soils. The bristle cut is designed to offer optimum cleaning with minimum effort. The quality natural bristle materials selected are thoroughly cleaned prior to manufacturing. TechBrush® handles are designed for a comfortable fit, while offering a variety of handle materials, including anodized aluminum, stainless steel, wood, and Delrin® material. The TechBrush® manufacturing process insures a durable long-lasting brush which will suit your specific needs.

## Chemical Components

---

This product does not contain any hazardous ingredients as per OSHA 29 CFR 1910.1200 Subpt.(z).

## Environmental Policy

---

Techspray® is committed to developing products to ensure a safer and cleaner environment. We will continue to meet and sustain the regulations of all federal, state and local government agencies.

## Packaging and Availability

---

Technical Cleaning Brushes are available in the following sizes:

2030-1 2031-1  
2032-1 2033-1

## Resources

---

Techspray® products are supported by a global sales, technical and customer services resources.

For additional technical information on this product or other Techspray® products in the United States, call the technical sales department at 800-858-4043, email [tsales@techspray.com](mailto:tsales@techspray.com) or visit our web site at: [www.techspray.com](http://www.techspray.com).

North America  
Tech Spray L.P.  
P.O. Box 949  
Amarillo, TX 79105  
800-858-4043  
email: [tsales@techspray.com](mailto:tsales@techspray.com)

Europe  
Techspray International  
UNIT 4, 44/46 Bunyan Road, Kempston  
Bedford MK42 8HL United Kingdom  
+44 (0) 1234 855443  
email: [tseurope@techspray.com](mailto:tseurope@techspray.com)

Countries Outside US  
Call to locate a distributor  
in your country.

Important Notice to Purchaser/User: The information in this publication is based on tests that we believe are reliable. The results may vary due to differences in tests type and conditions. We recommend that each user evaluate the product to determine its suitability for the intended application. Conditions of use are outside our control and vary widely. Techspray's only obligation and your only solution is replacement of product that is shown to be defective when you receive it. In no case will Techspray® be liable for any special, incidental, or consequential damages based on breach of warranty, negligence or any other theory.



Tech Spray, L.P.  
P.O. Box 949  
Amarillo, TX 79105  
[www.techspray.com](http://www.techspray.com)

[English MSDS](#)  
[French MSDS](#)  
[German MSDS](#)  
[Italian MSDS](#)  
[Spanish MSDS](#)



	2030	2031	2032	2033	2034	2035	2036
Bristle Length	1/8"	1/4"	1/2"	7/16"	1/8"	1/4"	7/16"
Bristle Width	1/16"	3/16"	3/8"	3/8"	1/16"	3/16"	3/8"
Bristle Trim	1/8"	A-1/2" B-1/4"	A-1/4" B-3/16"	3/4"	1/8"	A-1/2" B-1/4"	3/4"
Bristle Material	Goat Hair	Horse Hair	Horse Hair	Horse Hair	Hog Bristle	Hog Bristle	Hog Bristle
Bristle Retention	Machine Stamped	Machine Stamped	Machine Stamped	Machine Stamped	Machine Stamped	Machine Stamped	Machine Stamped
Handle Material	Stainless Steel	Stainless Steel	Zinc Plated Steel	Zinc Plated Steel	Stainless Steel	Stainless Steel	Zinc Plated Steel
Handle Length	3 1/2"	4 1/2"	4 1/2"	4 1/2"	3 1/2"	4 1/2"	4 1/2"
Bulk Pack	6	6	6	6	6	6	6