

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [5000271641](#)
Status: **Contact Molex**
Overview: [slimstack_mm016_pitch](#)
Description: 0.40mm (.016") Pitch Board-to-Board SlimStack™ Plug, Surface Mount, Dual Row, Vertical, 0.95mm (.037") Mated Height, with Friction Lock, Lead-free, 16 Circuits, Reel Size Diameter 330mm, Reel Quantity 2,000

Documents:

[3D Model](#) [Product Specification PS-500024-011 \(PDF\)](#)
[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

General


Product Family	PCB Headers
Series	500027
Application	Board-to-Board, Signal
Comments	Solder Tab Plating: Lead-free, Tin
Overview	slimstack_mm016_pitch
Product Name	SlimStack™

Physical

Breakaway	No
Circuits (Loaded)	16
Circuits (maximum)	16
Color - Resin	Natural
Durability (mating cycles max)	10
First Mate / Last Break	No
Glow-Wire Compliant	No
Guide to Mating Part	Yes
Keying to Mating Part	None
Lock to Mating Part	Yes
Mated Height	0.95mm (.037")
Material - Metal	Phosphor Bronze
Material - Plating Mating	Gold
Material - Plating Termination	Gold
Material - Resin	High Temperature Thermoplastic
Number of Rows	2
Orientation	Vertical
PC Tail Length	0.47mm (.019")
PCB Locator	No
PCB Retention	Yes
Packaging Type	Embossed Tape on Reel
Pitch - Mating Interface	0.40mm (.016")
Pitch - Termination Interface	0.40mm (.016")
Plating min - Mating	0.102µm (4µ")
Plating min - Termination	0.035µm (1.2µ")
Polarized to Mating Part	No
Polarized to PCB	No
Shrouded	Partial
Stackable	No
Temperature Range - Operating	-25°C to +85°C
Termination Interface: Style	Surface Mount

Electrical

Current - Maximum per Contact	0.1A
Voltage - Maximum	50V



EU RoHS

ELV and RoHS Compliant
REACH SVHC Contains SVHC: No
Low-Halogen Status Not Reviewed

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
 For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

500027Series

Mates With

500024 SlimStack™ Board-to-Board Receptacle

Material Info

Country of Origin

JP

Reference - Drawing Numbers

Packaging Specification

Product Specification

SPK-500027-001

PS-500024-011, RPS-500024-019, RPS-500024-025,
RPS-500024-030, RPS-500024-031, RPS-500024-032,
RPS-500024-034, RPS-500024-038, RPS-500024-039,
RPS-500024-040, RPS-500024-041

Sales Drawing

SD-500027-028, SD-500027-029

This document was generated on 11/15/2010

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION