



SLIDER AND ROTARY CONTROL KNOBS


Slider Control Knobs



A new low profile slider knob designed to offer you the best combination of appearance, "feel" and price. Available in seven different colours. Matt finish with marker line.



P776-2 Fits shaft types




Specify colour using code at bottom of page.


P776-5 Fits shaft type




Specify colour using code at bottom of page.



A higher profile slider knob. Available in seven different colours.



P772-2 Fits shaft types



Specify colour using code at bottom of page.

P772-5 Fits shaft type



Specify colour using code at bottom of page.




Colour Code for Part Number Suffixes.

	1	Red
	2	Green
	3	Yellow/White line
	4	Blue
	5	Black
	6	White
	7	Grey
	8	Yellow/Black line
	9	Brown
	0	Beige

For example
 Grey knob cap
 with line is
 P863-27 for
 a 19mm knob.

Samples available on request.

Rotary Control Knobs



P860 RANGE

A matt textured, ergonomically designed range of rotary Knobs with the option of nine different colour caps. The range covers $\frac{1}{4}$ ", 4mm and 6mm diameter spindles.

PUSH-ON FIXING

- P859-02** 15mm dia knob body – Matt black – fits 4mm flatted shaft.
- P859-12** 15mm dia knob body – Matt brown – fits 4mm flatted shaft.
- P861-01** 19mm dia knob body – Matt black – fits $\frac{1}{4}$ " flatted shaft.
- P861-11** 19mm dia knob body – Matt brown – fits $\frac{1}{4}$ " flatted shaft.
- P861-03** 19mm dia knob body – Matt black – fits 6mm flatted shaft.
- P861-13** 19mm dia knob body – Matt brown – fits 6mm flatted shaft.
- P860-01** 29mm dia knob body – Matt black – fits $\frac{1}{4}$ " flatted shaft.
- P860-11** 29mm dia knob body – Matt brown – fits $\frac{1}{4}$ " flatted shaft.
- P860-03** 29mm dia knob body – Matt black – fits 6mm flatted shaft.
- P860-13** 29mm dia knob body – Matt brown – fits 6mm flatted shaft.

GRUB SCREW FIXING

- P862-01** 19mm dia knob body – Matt black – fits $\frac{1}{4}$ " shaft.
- P862-11** 19mm dia knob body – Matt brown – fits $\frac{1}{4}$ " shaft.
- P862-02** 19mm dia knob body – Matt black – fits 4mm shaft.
- P862-12** 19mm dia knob body – Matt brown – fits 4mm shaft.
- P862-03** 19mm dia knob body – Matt black – fits 6mm shaft.
- P862-13** 19mm dia knob body – Matt brown – fits 6mm shaft.



COLOURED KNOB CAPS FOR P860 RANGE

- P864-2**. Knob Cap – with line for 15mm dia knobs.
- P863-2**. Knob Cap – with line for 19mm dia knobs.
- P865-2**. Knob Cap – with line for 29mm dia knobs.

Specify colour using code at bottom of previous page.

P870 RANGE

A new control knob range for those designers requiring a low profile.





PUSH-ON FIXING

- P870-01** 19mm dia knob body – Matt black – fits $\frac{1}{4}$ " flatted shaft.
- P870-11** 19mm dia knob body – Matt brown – fits $\frac{1}{4}$ " flatted shaft.
- P870-03** 19mm dia knob body – Matt black – fits 6mm flatted shaft.
- P870-13** 19mm dia knob body – Matt brown – fits 6mm flatted shaft.

COLOURED KNOB CAPS FOR P870 RANGE

- Z863-2**– Knob cap with line for 19mm dia P870 range.

Specify colour using code at bottom of previous page.



P850 RANGE

This push-on control knob range has been designed with an integral wing to ensure positive sight and touch alignment.

PUSH-ON FIXING

- P850-01** – Knob body – matt black with white marker – fits $\frac{1}{4}$ " flatted shaft.
- P850-03** – Knob body – matt black with white marker – fits 6mm flatted shaft.