



*it's all in the bag... Rod Sets*



**United Kingdom Main Distribution Centre**  
Wharf Approach, Aldridge,  
Walsall, West Midlands,  
WS9 8BX United Kingdom  
Tel: +44 (0)1922 458151  
Fax: +44 (0)1922 743053  
E-Mail: [distribution@hellermannityton.co.uk](mailto:distribution@hellermannityton.co.uk)

**Northern Ireland Distribution Centre**  
Units 1 & 2, Graham Industrial Park,  
Dargan Crescent, Belfast  
BT3 9JP Northern Ireland  
Tel: +44 (0)2 890 775 005  
Fax: +44 (0)2 890 781 456

**Ireland**  
Unit 77, Cherry Orchard Industrial Estate,  
Ballyfermot, Dublin 10, Ireland  
Tel: +353 (0)1 626 8267  
Fax: +353 (0)1 626 8022  
E-Mail: [sales@hellermannityton.ie](mailto:sales@hellermannityton.ie)

For further information on our complete product range please visit our website:  
[www.hellermannityton.co.uk](http://www.hellermannityton.co.uk)

## Rod Sets

HellermannTyton's Rod Sets have been specifically designed to be a time saving device to assist with many types of cable installation applications. This equipment can tackle some of the most difficult tasks users will encounter, routing, pulling and retrieving cables in the fastest and most economical way possible.

The rods are available in three different sets; the Deluxe set, the Standard set and the Handy set. Each comes complete with a light weight easy to carry bag and the Deluxe set and Handy set with a shoulder strap and carrier strap respectively, which makes transporting the sets very simple. We also offer a full range of attachments which include cable grips, whisk, magnet, beam with battery provided, an accessory kit and spare rod pairs.

### Deluxe Set



Includes a light weight carry bag with shoulder strap

**Article Number:** 897-90001  
**Type:** CS-SD  
**Description:** The most comprehensive set for carrying out larger installations  
**Content Rods:** 2 x 4mm x 1000mm (white)  
 6 x 5mm x 1000mm (red)  
 2 x 6mm x 1000mm (blue)  
**Rod Capacity (m):** 10  
**Content:**  
**Attachments:** 150mm white flexi lead, split ring, gender changer, tuff hook, mini eye, domed bullet, flat bullet, beam, single magnet.

### Standard Set



Includes a light weight easy access carry bag

**Article Number:** 897-90000  
**Type:** CS-SB  
**Description:** Designed to perform standard cable installation  
**Content Rods:** 10 x 4mm x 1000mm (white)  
**Rod Capacity (m):** 10  
**Content:** 150mm white flexi lead, gender changer, tuff hook, mini eye.  
**Attachments:**

### Handy Set



**Article Number:** 897-90003  
**Type:** CS-SH  
**Description:** Suitable for tool box storage  
**Content Rods:** 1 x 4mm x 400mm (white)  
 2 x 5mm x 400mm (red)  
 1 x 6mm x 400mm (blue)  
**Rod Capacity (m):** 1.6  
**Content:** 400mm white flexi lead, domed bullet, mini hook, mini eye.  
**Attachments:**


## Attachments



**Whisk**  
**Article No:** 897-90018  
**Type:** CS-AW  
**Description:** Enables cables to glide over rough and uneven surfaces



**Beam**  
**Article No:** 897-90016  
**Type:** CS-AB  
**Description:** Useful for inspection purposes in dark surroundings.  
 Includes a AAAA battery



**Cable Grips**  
**Article No:** 897-90026, 897-90027  
**Type:** CS-ACG0415, CS-ACG1630  
**Description:** CS-ACG0415 contains 3 cable grips suitable for a range of cable diameters from 4 to 15mm. CS-ACG1630 contains 2 cable grips suitable for a range of cable diameters from 16 to 30mm.




**Strong Magnet**  
**Article No:** 897-90015  
**Type:** CS-AMG2  
**Description:** A helpful tool to lift metal objects up to 2.5kg in weight and can be used in conjunction with the chain to aid location.



**Attachment Kit**  
**Article No:** 897-90004  
**Type:** CS-SA  
**Description:** Includes a 150mm long flexi lead, gender changer, mini hook, tuff hook, mini eye, split ring, round bullet, flat bullet, single magnet and chain.

## Technical Information

Technical Table		OD (mm)
Colour	Flexibility	
Blue (BU)	strong	6
Red (RD)	medium	5
White (WH)	flexible	4
Semi-transparent white	fully flexible	5



## Performance Criteria

The Rods are available in a number of different colours. Each colour signifies the external diameter of the Rod. Different diameters of Rod have a different flexibility and consequently differing bending radius.

The maximum recommended bending radius for each of the Rods is shown in the diagram on the left.

Rods made of glass reinforced plastic (GRP) are able to pull a cable weight of up to 80 kg.

## Typical Applications

