

George GVE-370

Yes, designed to be a true all-in-one cleaning machine, equally at home whether it's:

- Dry vacuuming clean floors
- Wet pick-up vacuuming dry floors
- Extraction carpet cleaning clean carpets
- Extraction hard floor cleaning cleaner and drier floors
- Extraction upholstery cleaning clean furnishings

Yes, the GEORGE machine has been designed with the most comprehensive range of standard accessories available. Whatever your cleaning needs, be it pictures or pelmets, carpets or curtains, if the washing machine overflows, or the sink is blocked, or whether you simply decide to clean all the carpets in the house - GEORGE is equipped to answer the call.

GEORGE means true power cleaning, combining both the highly efficient turboflo' vacuum turbine and the powerflo' injection pump system to ensure truly professional results.

The GEORGE design is in itself based entirely on our Cleantec professional range of machines, designed to work extensively and for long hours and functioning to a professional standard.

When it comes to dry vacuuming you have big filters, you can use disposable paper bags, and you have a superb combination floor nozzle.

In the wet mode, a simple exchange of the filter for the safety float valve allows any number of wet tasks to be achieved, be it blocked sinks, overflowing washing machines, burst pipes etc.




When it comes to carpet cleaning you will very quickly see the superb results achieved by the simultaneous injection of cleaning solution into the carpet, combined with high vacuum extraction. This is professional cleaning at its best!

Hard floor cleaning with the vacuumop nozzle is simplicity itself, leaving a large floor clean and dry in a matter of moments.

Upholstery and fabric cleaning with the upholstery cleaning head is something to behold as you see the dirt disappearing before your very eyes.











GEORGE - the even more complete vacuum cleaning system.

The versatile Vacuumop head leaves floors clean and dry in a matter of moments.



Numatic INTERNATIONAL


DATA... DATA... DATA...

				
Motor	Power	Airflow	Suction	Capacity Dry
1000W	230/120V AC50/60 Hz	43.5 litres/sec.	2100mm	15 litres
				
Capacity Wet	Extraction Solution	Cleaning Range	Weight	Size
9 litres	6L / 6L	23.2m (76ft.)	9.5 Kgs	355 x 355 x 455mm


Motor watts shown are MAXIMUM, not watts. However, in accord with the specific requirements of the majority of International Approved Agencies, rating tables on machines show MEAN operational watts, being the average watts consumed during normal use. i.e. 1000 watts MAX = 500 watts MEAN.

Distributed by: 23 1332/96121A


Numatic International Limited, Chard, Somerset, TA20 2BB
 Tel: 01460 68480 Fax: 01460 68560
 •Sales – Tel: 01460 68600 Fax: 01460 68458




Powerflo' pump system




3 stage filtration to hospital standards.



High efficiency Turboflo' powerhead





Overflow protected wet pick-up system



The dual clean-and-dirty liquid containers and safety float valve.

Pail handle for easy emptying



4Wheel tracking mobility

George

