

(888-6735)

357 5457

SYSTEM UPGRADE KIT

MOTHERBOARD

JETWAY 618 AF INTEL 815 FC PGA c/w SOUND FEATURES [SPECIFICATION]
Support Socket 370 processor for Intel Pentium III Coppermine TM (FCPGA) , Celeron TM (FCPGA,PPGA) Processor,Optimized for 133MHz Front Side Bus Frequency
Intel 82815E and 82801BA (ICH2) chipset
Support ATA 100
On chip VGA Support Hardware DVD Playback
Extend AGP Slot Support 4X AGP
PCI 3D Audio Digital Sound Effect
PC'99 Ready & PC'99 Colourful I/O Ports Design
Support USB Controller & PS/2 Mouse , Standard IR (infrared) Function
Provide extra " three-wire" fans connectors
Support TV-Out/LCD Panel (Optional)
Support Smart Card Security (Optional)
JumperLess
Frequency Magic Setting
PC Health Monitoring On Post Screen
Magic Install
Y2K Compliant
ACPI Supporting For OS Directed Power Management

PROCESSOR

Modem Ring remote wake up
RTC alarm wake up
Wake on LAN For OS
Support software suspend & power off
Power Button Ride (Instant off or Delay 4 second power off)
INTEL CELERON 600MHz
The features of the 0.18 micron Celeron include:
0.18 micron manufacturing process.
Flip Chip Pin Grid Array (FC-PGA) packaging.
Intel's Advanced Transfer cache design (128 Kb).
Streaming SIMD instructions.

MEMORY

1.50v core voltage.
66 MHz Front Side Bus.
32 Kb Level 1 cache.
128Mb PC100MHz DIMMS
PC 100 specification

HARD DRIVE

High Quality Major Manufacturer Branded
20GB 5400 rpm GENERIC -
EIDE ATA/66 HD 5400RPM 3.5LP

FLOPPY DRIVE

1.4Mb 3.5 inch GENERIC

CD ROM DRIVE

LG 52X SPEED GENERIC
• Disk Data Capacity : Mode 1: 656MB / Mode 2: 748MB
• Data Buffer Size: 128 Kbytes
• Power Requirement : DC 5V+- 5%, DC 12V+- 5%
• Mount Position : Both Horizontal and Vertical
• Dimensions : 5.87"(W) x 1.65"(H) x 7.74"(D)
• 52X-MTRP Speed – 7800KB/sec. Data Transfer Rate
• Multi-Read Function: Can Read CD-RW Media Data
• ATAPI IDE Interface
• Complies with MPC 3

	<ul style="list-style-type: none"> • User-friendly Front Panel with Audio Play/Skip Track Control • Compatible with CD-DA, CD-ROM/XA, CD-I/MPEG, Photo CD, Karaoke CD, CD-Extra (CD+), I-TRAX CD, CD-RW, Packet write • Vertical Mount Applicable • Ultra DMA 33 Supported
GRAPHICS CARD	ONBOARD See motherboard specification.
SOUND CARD	ONBOARD See motherboard specification
SPEAKERS	80WATT GENERIC SPEAKERS Standard mains powered speakers fully CE compliant
MODEM	INTERNAL 56K ROCKWELL DATA FAX VOICE Supports V.90 for speeds up to 56,000 bit/s Sends and receives faxes with speeds up to 14,400 bit/s Top-rated communications software
MONITOR	NOT INCLUDED
KEYBOARD & MOUSE	PS2 WIN95 KEYBOARD & PS2
OPERATING SYSTEM	NOT INCLUDED
CASE	MIDI TOWER ATX Mdi ATX Tower case, comes with standard 300 watt PSU, 3x 5.25" bays; 1x 3.5" bay;
WARRANTY	1 YEAR PARTS AND LOBOUR 2 YEARS RETURN TO BASE