



EDL Lighting limited

Redbrook Lane, Brereton, Rugeley, Staffordshire WS 15 1QU
Tel: 01889 582112 Fax: 01889 584012 e mail: sales@edl-lighting.co.uk
Web: www.edl-lighting.co.uk

T5E Luminaire

The T5E range is a general purpose-designed, robust, durable industrial task light, providing a long trouble-free life in demanding conditions

Version: T5E-HTB-5U-IP44-50W-12/24V

Order Code 00582



Dimensional Line Diagram T5E HTB
When Available

Primary voltage:	12/24v
Secondary voltage:	Not applicable
Lamp type:	Halogen
Wattage:	Max 50 watt
Lamp base type	GU5.3
Switch fitted Yes/No:	Yes
Switch location:	On Head
IP Rating	IP44
Base Type:	Universal Base
Fixing:	Can be horizontal or vertically mounted
No of arms:	0
Length of arms	not applicable
Arm Material:	Cast aluminum knuckle joint
Shade size and material:	127mm diameter spun aluminum
Shield fitted:	Yes
Shield material	Glass
Visor fitted:	No
Articulation movement:	See diagram
Joint type:	Friction adjustable
Trailing cable:	Not fitted
Plug fitted	No
Manufacturing Standard:	BS EN 60598 etc
RHOS compliant	Not applicable
WEE Compliant	Not applicable
Finish & Colour:	Powder coated Light Grey (RAL7035)



EDL Lighting limited

Redbrook Lane, Brereton, Rugeley, Staffordshire WS 15 1QU
Tel: 01889 582112 Fax: 01889 584012 e mail: sales@edl-lighting.co.uk
Web: www.edl-lighting.co.uk

The T5E range is a general purpose-designed, robust, durable industrial task light, providing a long trouble-free life in demanding conditions

Version: T5E-HTB-5U-IP44-50W-12/24V

Order Code 00582

Features

Cast Aluminium head 127mm dia with adjusting handle and shield

High quality friction arm joints - tested to 30,000 movements, move easily, yet retain position

Vibration resistant mountings, arms and lamp holders for demanding operating conditions

Versatile and flexible positioning, relative to subject, based on a variety of arm length combinations


Shade design maximises the light output from the lamp

Cable totally enclosed within the unit

All metal parts are coated in tough chip resistant epoxy polyester powder paint

Switch located on head for ease of operation

General T5E Arm Articulation Diagram



MT Transformer



Clamp Assy with Cable/Euro Plug



Clamp assy with cable/3 Pin Plug

