




RMQ 16 Illuminated Selector Switch Actuators and Contact Elements

 Square style
Front dimensions:

18x18 mm

25x25 mm

 Function
= Stay-put
 = Spring-
return

Thumb-
grip
colour


Type
Article no.

Type
Article no.

Price
See Price
List

Std.
pack

Notes



Accessories


Page







Assembly aids 03/077
and accessories

Control Circuit Devices

Illuminated selector switch actuators IP 65, 2 positions


With anti-rotation feature with filament bulb, 24 V



























Function	Angle	Thumb-grip colour	Type Article no.	Type Article no.	Price	Std. pack
 45°	45°		Q18LWK1-WS/WB 038978	Q25LWK1-WS/WB 040379		5 off
 45°	45°		Q18LWK1-RT/WB 038930	Q25LWK1-RT/WB 040378		
 45°	45°		Q18LWK1-GN/WB 038883	Q25LWK1-GN/WB 040377		
 45°	45°		Q18LWK1R-WS/WB 039335	Q25LWK1R-WS/WB 040476		
 45°	45°		Q18LWK1R-RT/WB 039248	Q25LWK1R-RT/WB 040381		
 45°	45°		Q18LWK1R-GN/WB 039247	Q25LWK1R-GN/WB 040380		

Illuminated selector switch actuators IP 65, three positions

With anti-rotation feature and filament bulb, 24 V







Function	Angle	Angle	Thumb-grip colour	Type Article no.	Type Article no.	Price	Std. pack
45°  45°	45°	45°		Q18LWK3-WS/WB 072334	Q25LWK3-WS/WB 072346		5 off
45°  45°	45°	45°		Q18LWK3-RT/WB 072335	Q25LWK3-RT/WB 072347		
45°  45°	45°	45°		Q18LWK3-GN/WB 072336	Q25LWK3-GN/WB 072348		
45°  45°	45°	45°		Q18LWK3R-WS/WB 072337	Q25LWK3R-WS/WB 072349		
45°  45°	45°	45°		Q18LWK3R-RT/WB 072338	Q25LWK3R-RT/WB 072350		
45°  45°	45°	45°		Q18LWK3R-GN/WB 072339	Q25LWK3R-GN/WB 072351		
45°  45°	45°	45°		Q18LWK3R1-WS/WB 072340	Q25LWK3R1-WS/WB 072352		
45°  45°	45°	45°		Q18LWK3R1-RT/WB 072341	Q25LWK3R1-RT/WB 072353		
45°  45°	45°	45°		Q18LWK3R1-GN/WB 072342	Q25LWK3R1-GN/WB 072354		
45°  45°	45°	45°		Q18LWK3R2-WS/WB 072343	Q25LWK3R2-WS/WB 072355		
45°  45°	45°	45°		Q18LWK3R2-RT/WB 072344	Q25LWK3R2-RT/WB 072356		
45°  45°	45°	45°		Q18LWK3R2-GN/WB 072345	Q25LWK3R2-GN/WB 072357		


Contact elements¹⁾

Admissible operating voltage: 5-250 V



Symbol	Thumb-grip colour	Type Article no.	Type Article no.	Price	Std. pack
1 M 		E10 090351	E10 090351		50 off
1 B 		E01 090401	E01 090401		50 off

Notes

¹⁾  x = Sequence number on front element
y = Function number on contact element