

Wiha ESD application sets.

The right tool for any application.



ESD application sets.



NEW

Wiha operator kit, 5 pcs.
Dissipative tools, electrostatically discharging.

Design: ESD tools manufactured according to IEC 61340-5-1.
 Maximum protection of electronic components from electrostatically discharging tools and packaging.

Pouch: Handy leather bag, ideal for all overall pockets.
 Safe storing of tools directly in the overall.
 No danger of injury to users or damage to workwear from sharp or loose tools in overall pockets.

Content:

- Professional ESD universal tweezers** (ZP 01 0 14 series)
- Wiha Precision ESD screwdrivers:**
 - Slotted screwdriver, 2.5x50 (272 series)
 - Phillips screwdriver, PH0x50 (273 series)
- SMD belt shears** (246 series)
- Dust and dirt brush** (246 series)

Application: The most important tools for automatic insertion machines in continuous operation.

Order-No.	Series	
33504 5	9300-015	1

ESD application sets.



NEW

Wiha electronic assembling kit, 9 pcs.
Dissipative tools, electrostatically discharging.

Design: ESD tools manufactured according to IEC 61340-5-1.
 Diagonal cutters without facet especially suitable for clean and smooth cutting of wired components.
 Wide selection of current screwdrivers for electronic applications.
 With universal tweezers for assembly of PCBs or for SMD re-work activities.
 Robust and space-saving storage of tools.

Pouch:

Content:

- Diagonal cutter without facet**, 115 mm (Z 41 3 04 series)
- Electric needle nose pliers**, 120 mm (Z 36 0 04 series)
- Professional ESD universal tweezers** (ZP 01 0 14 series)
- Wiha Precision ESD screwdrivers:**
 - Slotted screwdriver, 2.0x40 / 2.5x50 (272 series)
 - Phillips screwdriver, PH00x40 / PH0x50 (273 series)
 - TORX® screwdriver, T5x40 / T6x40 (278 series)

Application: The most important tools for hand assembly of electronic components and re-work activities.

Order-No.	Series	
33505 2	9300-016	1



NEW

Wiha electronic service kit, 8 pcs.
Dissipative tools, electrostatically discharging.

Design: ESD tools manufactured according to IEC 61340-5-1.
 Diagonal cutters with facet, suitable for cutting of thin and hard wires.
 Wide selection of current reversible blades for electronic applications.
 Light and compact design.

Pouch: Light and space-saving storage of tools.

Content:

- Diagonal cutter with facet**, 115 mm (Z 44 1 04 series)
- Electric needle nose pliers**, 120 mm (Z 36 0 04 series)
- Professional ESD universal tweezers** (ZP 01 0 14 series)
- SYSTEM 4 SoftFinish® telescopic ESD handle**
- SYSTEM 4 reversible blades** (269 series):
 - Slotted/ Phillips: 2.0 – PH00 / 2.5 – PH0
 - TORX®: T5 – T6
 - Hexagon/ hexagon ball end: SW 1.5 – SW 1.5

Application: Set combination ideally suited to maintenance work with electronic components.

Order-No.	Series	
33506 9	9300-017	1

Wiha Info

Wiha application sets:

- Tool sets especially matched to your application
- Orderly, clearly laid out arrangement of the most common tools
- No additional ballast due to unnecessary tools
- Direct input of the experience of final users already integrated in product development

