

## PC Cable-Check® Pro

The *best selling* PC Cable-Check® has been upgraded and now tests PC, Mac, video, network and coaxial cable assemblies.

**New**

### Function:

This powerful troubleshooting tool maps cables and detects good connections and any opens, shorts, and crosses in the cable.

### Advantages:

- Universal tester for all computer cables
- Quickly & easily troubleshoot cables to eliminate the cable as the source of the problem
- True cable mapping
- Easy to read and understand with LED indicator lights
- New rugged case with built-in handle for easy transport
- Auto scan or manual scan modes.

### Features & Benefits:

- Rubber feet grip to desk or bench to prevent slipping
- Power shuts off after 30 seconds of non-use to extend battery life
- Tests over 20 types of patch cables up to 1,000' in length:
  - LAN & telephone
  - Serial
  - Coax 50 & 75\* ohm
  - USB
  - VGA
  - Mini-USB
  - S-video
  - FireWire
  - PS/2 keyboard
  - Parallel printer(\*Note: up to 600' in length)
- 9V battery included
- One-year warranty



**Ordering/Description**  
PC Cable-Check® Pro

**Part No.**  
1577

**Paladin Tools®**

# PC Cable-Check® Pro

## Nitty Gritty:

Tests cables with the following terminations:

- **Modular plugs:** RJ45, RJ11, RJ12 shielded & unshielded (UTP/STP)
- **Coaxial:** BNCs and CATV "F"s (BNC-to-F adapter required; not included)
- **D-Sub:** 9-, 15- and 25-pin
- **HD-Sub:** 15-pin
- **USB:** A, B and mini 5-pin
- **1394 firewire:** 4- and 6-pin
- **Mini-DIN:** 4- and 6-pin
- **Centronics:** 36-pin printer

## Specifications:

### Maximum Cable Length:

Cable Type	Max. Cable Length
D-sub	1,000' (305 m)
Phone and data	1,000' (305 m)
USB	1,000' (305 m)
Firewire	1,000' (305 m)
DIN & mini-DIN	1,000' (305 m)
Centronics	1,000' (305 m)
Coax - 50 ohm	1,000' (305 m)
Coax - 75 ohm	600' (183 m)


**Power Requirements:** 9VDC battery (one) included

**Output Signal:** 8VDC@10mA

**Auto power-off:** 30 seconds of non-use

**Dimensions:** 11.0" H X 6.65" W X 1.60" D

**Weight:** 1.7 lbs.



LIMITED  
**One-year**  
WARRANTY

**Paladin Tools®**  
connectool Inc., Virginia-USA

Support: 800.272.8665

001.804.550.1121

Web: [www.paladin-tools.com](http://www.paladin-tools.com)

Fax: 800.272.5257

001.804.550.0610

Email: [paladin@paladin-tools.com](mailto:paladin@paladin-tools.com)