




THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION 20  
 © COPYRIGHT 20 BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.



LOC	DIST	REVISIONS					
CM	00	P	LTR	DESCRIPTION	DATE	DWN	APVD
		0		RELEASED PER 063B-0331-01	17-DEC-01	KW	CJ



PANEL CUT-OUT




SCALE 5:1



40.88	37.20	36.85	12	1-1445048-2
37.88	34.20	33.85	11	1-1445048-1
34.88	31.20	30.85	10	1-1445048-0
31.88	28.20	27.85	9	1445048-9
28.88	25.20	24.85	8	1445048-8
25.88	22.20	21.85	7	1445048-7
22.88	19.20	18.85	6	1445048-6
19.88	16.20	15.85	5	1445048-5
16.88	13.20	12.85	4	1445048-4
13.88	10.20	9.85	3	1445048-3
10.88	7.20	6.85	2	1445048-2
DIM C	DIM B	DIM A	NO. OF POS.	PART NUMBER

RECOMMENDED PANEL THICKNESS 1.57-2.3.

2. PANEL MUST BE PUNCHED SO THAT HOUSING ENTERS THE PANEL IN THE SAME DIRECTION AS THE PUNCH.



<small>THIS DRAWING IS A CONTROLLED DOCUMENT FOR TYCO ELECTRONICS CORPORATION. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.</small>		DWN W. J. RUDY 29AUG2000 CHK W. DAVIS 29AUG2000 APVD W. DAVIS 29AUG2000	<b>AMP</b> Tyco Electronics Harrisburg, PA 17105-3608
DIMENSIONS: mm 	TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± 1 PLC ± 2 PLC ±0.13 3 PLC ± 4 PLC ± ANGLES ± FINISH -	NAME PLUG HOUSING, 2 TO 12 POSITION SINGLE ROW, PANEL MOUNT MICRO MATE-N-LOK™ PRODUCT SPEC - APPLICATION SPEC - WEIGHT -	SIZE A2 CAGE CODE 00779 DRAWING NO. 1445048 RESTRICTED TO - SCALE 6:1 SHEET 1 OF 1 REV 0
MATERIAL NYLON, UL94V-0 BLACK		CUSTOMER DRAWING	