

Metrinch® 6WD Socket Sets

321-7073 + 321-7139

~~321-613~~

PRODUCT NUMBER

SIZE DETAILS

PACK QUANTITY

LIST PRICE (Ex. VAT)

R.R.P. (Inc. VAT)

50-pc METRINCH Socket-and-Spanner Set (1/2", 3/8" and 1/4" Drive) Equivalent to a 126pc traditional set

This set contains 28 Metrinch 6WD sockets in 1/2", 3/8" and 1/4" drive, 15 accessories and 7 sizes of Metrinch 4WD combination spanners. All components are of chrome-vanadium steel, and meet the torque requirements of British Standard BS4006.

Metrinch sockets and spanners fit both metric and AF hexagons, and the majority Whitworth and BSF also. The "List of Contents" (below left) only gives metric sizes, because of lack of space.

However, the "Equivalency Table" (below right) does show the different types/sizes hexagons the same 6WD

socket or 4WD spanner will fit e.g. one 6WD socket fits 11mm; 7/16" AF; 3/16" WW and 1/4" BSF hexagons.



321-7073 + 321-7139

LIST OF CONTENTS HAS

1/2" DRIVE Ratchet handle with press-button instant socket release and flick-over lever to instantly reverse drive direction. Handle contoured for firm grip, with wipe-clean, all-polished surface for easy removal of oil, grease or sharp metal fragments. Breaker bar of 425mm (17") length for use when high-torque necessary to turn stubborn hexagons. 75mm (3"), "wobble" extension bar, 125mm (5") and 250mm (10") standard extension bars. "T" bar converter (for use with extension bars). 8 Metrinch 6WD sockets (17mm-32mm).

3/8" DRIVE Ratchet handle has all same features as 1/2" drive version. 38mm (1 1/2") "wobble" extension bar; 75mm (3") and 125mm (5") standard extension bars; Universal joint. 14mm and 10mm spark plug sockets. 7 standard length Metrinch 6WD sockets (10mm-17mm). 7 deep-wall Metrinch 6WD sockets (10mm-17mm).


1/4" DRIVE Long-shank nut driver with female square drive in end of handle. 6 Metrinch 6WD standard length sockets (5mm-10mm).

METRINCH 4WD COMBINATION SPANNERS. The 7 spanners have same capability for fitting differing types/sizes of hexagons as do 6WD sockets. (For further details of 4WD spanners, please see page 31). Metric sizes 10mm-19mm. For details of other types/sizes of hexagons 4WD spanners will fit.

6WD Socket



4WD Spanner



EQUIVALENCY TABLE

The socket or spanner which fits the Metric size shown below also fits the other hexagon sizes/types shown alongside e.g. one socket operates both 13mm and 1/2" AF hexagons

	MM	AF	WW	BSF	BA
•	5mm	3/16"	-	-	6
•	6mm	1/4"	-	-	4
•	7mm	9/32"	-	-	3
•	8mm	5/16"	-	-	2
•	9mm	11/32"	-	-	-
•	10mm	3/8"	-	-	-
•	11mm	7/16"	3/16"	1/4"	-
•	12mm	15/32"	-	-	-
•	13mm	1/2"	-	-	-
•	14mm	9/16"	1/4"	5/16"	-
•	16mm	5/8"	5/16"	3/8"	-
•	17mm	11/16"	-	-	-
•	19mm	3/4"	3/8"	7/16"	-
•	21mm	13/16"	7/16"	1/2"	-
•	22mm	7/8"	-	-	-
•	24mm	15/16"	1/2"	9/16"	-
•	25mm	1"	9/16"	5/8"	-
•	27mm	1 1/16"	5/8"	11/16"	-
•	28mm	1 1/8"	5/8"	11/16"	-
•	30mm	1 3/16"	1 1/16"	3/4"	-
•	32mm	1 1/4"	3/4"	7/8"	-

BW29/5000

as above

3

159.11

186.95