



# EDL Lighting limited


Redbrook Lane, Brereton, Rugeley, Staffordshire WS 15 1QU  
Tel: 01889 582112 Fax: 01889 584012 e mail: sales@edl-lighting.co.uk  
Web: www.edl-lighting.co.uk

## T21 Luminaire

The Task 21 range is a general purpose-designed, robust, durable industrial task light, providing a long trouble-free life in demanding conditions

Version: T21-SSS-5U-IP64-60W-ES

Order Code 00320



Primary voltage:	24v, 50v 110v 240v
Secondary voltage:	Not applicable
Lamp type:	Incandescent
Wattage:	Max 60 watt
Lamp base type	E27 Edison Screw
Switch fitted Yes/No:	Yes
Switch location:	On Head
IP Rating	IP64
Base Type:	Universal Base
Fixing:	Can be horizontal or vertically mounted
No of arms:	3
Length of arms	250 + 250 + 250mm
Arm Material:	Steel tube cast aluminum knuckle joint
Shade size and material:	127mm diameter spun aluminum
Shield fitted:	Yes
Shield material	Clear polycarbonate
Visor fitted:	Yes _ Moulded with handle
Articulation movement:	See diagram
Joint type:	Friction adjustable
Trailing cable:	Not fitted
Plug fitted	No
Manufacturing Standard:	BS EN 60598 etc
RHOS compliant	Not applicable
WEE Compliant	Not applicable
Finish & Colour:	Powder coated gunmetal grey



# EDL Lighting limited

Redbrook Lane, Brereton, Rugeley, Staffordshire WS 15 1QU  
Tel: 01889 582112 Fax: 01889 584012 e mail: sales@edl-lighting.co.uk  
Web: www.edl-lighting.co.uk

The T21 range is a general purpose-designed, robust, durable industrial task light, providing a long trouble-free life in demanding conditions

Version: T21-SSS-5U-IP64-60W-ES

Order Code 00320

## Features

High quality friction arm joints - tested to 30,000 movements, move easily, yet retain position

Vibration resistant mountings, arms and lamp holders for demanding operating conditions

Versatile and flexible positioning, relative to subject, based on a variety of arm length combinations

Shade design maximises the light output from the lamp

Shade is equipped with anti-glare visor for greater user comfort


Cable totally enclosed within the unit

All metal parts are coated in tough chip resistant epoxy polyester powder paint

Switch located on head for ease of operation

The head is moulded from strong shock resistant thermoplastic material, which acts as an electrical insulator

## General Task 21 Arm Articulation



## MT Transformer



## Clamp Assy with Euro Plug



## Clamp assy with 3 Pin Plug

