

Packing unit **Order-no.**

Packing unit **Order-no.**

TV/AUDIO

Aerial sockets

NEW



Aerial connector box TV			
brown, mat, with solder connection	10	09 4511 25 11	
anthracite, mat, with solder connection	10	09 4511 25 15	
grey, mat, with solder connection	10	09 4511 25 16	
polar white, mat, with solder connection	10	09 4511 25 12	
brown, mat, with connection in F system	10	*09 4581 25 01	
anthracite, mat, with connection in F system	10	*09 4581 25 05	
grey, mat, with connection in F system	10	*09 4581 25 06	
polar white, mat, with connection in F system	10	*09 4581 25 02	

DIN 45325



Aerial connector box SAT			
brown, mat	10	09 4519 25 01	
anthracite, mat	10	09 4519 25 05	
grey, mat	10	09 4519 25 06	
polar white, mat	10	09 4519 25 02	

- with double F-socket



Aerial connector box TV/radio			
polar white, mat	10	09 4561 25 02	

- with IEC and F socket
- with connection in F system



Aerial connector box radio/SAT			
brown, mat	10	09 4560 25 01	
anthracite, mat	10	09 4560 25 05	
polar white, mat	10	09 4560 25 02	

- with IEC and F socket
- with connection in F system

DATA-/TELECOMMUNICATIONS

Supporting plates for modular jacks



Supporting plate for 2 MINI-COM modules			
anthracite, high-gloss	10	09 4559 25 05	
grey, high-gloss	10	09 4559 25 07	
polar white, high-gloss	10	09 4559 25 09	

for order-no. 1980, 1981, 1983, 1984, 1989
dummy module see module inserts / accessories order no. 1990

Modules:
Panduit

- for mini jacks cat.3, cat.5, cat.5e and cat.6
- for optical fibre OPTI JACKs
- for Simplex-ST and Duplex-SC fibre-optic couplings
- for BNC connector modules
- for cinch connector modules
- for DIN round connector SVHS modules
- for dummy modules 1gang
- with 30° oblique outlet

Cinch sockets

NEW



Cinch module set			
white/red	1	* 1989	

for order-no. 0945 59 25 .., 0945 .., 1427 ..
dummy module see accessories order no. 1990

- with 2 Cinch sockets and module carriers
- with tool free cutting terminals

Modular jacks



Mini jack 8pole			
black, RJ45, cat.3 ISDN-compatible	10	1980	
RJ45, cat.5, shielded (AWG 22-23)	10	# 1981	
RJ45, cat.5E shielded (AWG 22-24)	10	1984	
RJ45, cat.6, shielded	10	1983	

for order-no. 0945 59 .., 1427 ..

Cat.5 to DIN EN 50173-1:2003 and ISO/IEC 11801, 2nd edition

Cat.6 ISO/IEC 11801 2nd edition

Protective screen DIN EN 55022 class B

Colour coded to EIA/TIA 568A and 568B

- with insulation piercing terminals

Dummy module

NEW



Blank modul			
polar white, 1gang	1	* 1990	

for order-no. 0945 59 .., 0945 .., 1427 ..

Supporting plates for modular jacks



Supporting plate for AMP modular jacks 1gang			
anthracite, high-gloss	10	09 4557 25 05	
grey, high-gloss	10	09 4557 25 07	
polar white, high-gloss	10	09 4557 25 09	

for order-no. 1854

SL series toolless jack:

AMP;

Modular jacks:

Brand-Rex;

CobiNet;

EFB Electronic;

Schumann;

EMT modular jack:

AMP;

Standard 110 Connect jack:

AMP;

MT-RJ jack:

AMP;

Intracom;

Telena

- for AMP modular jacks series 110 Connect cat.3, cat.5, cat.5e and cat.6