

Mounted points

Schleifstifte

Meules sur tige

Muelas de corindón



Aluminium oxide / Aluminiumoxid / Oxyde d'aluminium / Óxido de aluminio

Pink / Rosa / Rose / Rosa

Shape W / Form W / Forme W / Forma W

For actual size shape reference see pages 121-124

Für genaue Größenformkennung siehe Seiten 121-124

Pour le gabarit grandeur nature, voir pages 121-124

Para la referencia a tamaño / forma real, véanse las páginas 121-124

| | shape/Form/Forme/Forma | W200 | W201 | W203 | W204 | W205 | W207 | W208 | W215 |
|----------|------------------------|-------------|-------------|-------------|-------------|-------------|-------------|-------------|-------------|
| | Part Nr | GHW20006PKM | GHW20106PKM | GHW20306PKM | GHW20406PKM | GHW20506PKM | GHW20706PKM | GHW20806PKM | GHW21506PKM |
| d1 | 19mm | 19mm | 19mm | 19mm | 19mm | 19mm | 19mm | 25mm | |
| l1 | 3mm | 6mm | 13mm | 19mm | 25mm | 38mm | 51mm | 3mm | |
| d2 | 6mm | 6mm | 6mm | 6mm | 6mm | 6mm | 6mm | 6mm | |
| | 47,750 | 47,750 | 47,750 | 42,750 | 34,500 | 24,000 | 18,750 | 38,200 | |
| | 10 | 10 | 10 | 10 | 10 | 10 | 10 | 10 | |
| IPC Code | 51 | 51 | 51 | 51 | 51 | 51 | 51 | 51 | |

| | shape/Form/Forme/Forma | W216 | W218 | W220 | W222 | W226 | W227 | W228 | W230 |
|----------|------------------------|-------------|-------------|-------------|-------------|-------------|-------------|-------------|-------------|
| | Part Nr | GHW21606PKM | GHW21806PKM | GHW22006PKM | GHW22206PKM | GHW22606PKM | GHW22706PKM | GHW22806PKM | GHW23006PKM |
| d1 | 25mm | 25mm | 25mm | 25mm | 32mm | 32mm | 32mm | 32mm | |
| l1 | 6mm | 13mm | 25mm | 50mm | 10mm | 13mm | 19mm | 32mm | |
| d2 | 6mm | 6mm | 6mm | 6mm | 6mm | 6mm | 6mm | 6mm | |
| | 38,200 | 38,200 | 25,500 | 15,900 | 29,840 | 29,840 | 29,840 | 20,400 | |
| | 10 | 10 | 10 | 10 | 10 | 10 | 10 | 10 | |
| IPC Code | 51 | 51 | 51 | 51 | 51 | 51 | 51 | 51 | |

| | shape/Form/Forme/Forma | W232 | W236 | W242 |
|----------|------------------------|-------------|-------------|-------------|
| | Part Nr | GHW23206PKM | GHW23606PKM | GHW24206PKM |
| d1 | 32mm | 38mm | 50mm | |
| l1 | 50mm | 13mm | 25mm | |
| d2 | 6mm | 6mm | 6mm | |
| | 14,250 | 25,130 | 19,100 | |
| | 10 | 10 | 10 | |
| IPC Code | 51 | 51 | 51 | |