

### Share large files at faster network speeds, with maximum efficiency

The **Belkin 5-Port Gigabit Switch** allows you to easily upgrade your network to achieve gigabit transfer speeds. Backward-compatible with your existing 10/100 network, this Switch simply plugs in for instant high performance. It provides your servers and workstations the capacity to transfer large video, audio, and graphic files throughout your network—at gigabit speeds.


Engineered for compact convenience, it features a durable metal chassis and quiet, fan less design that easily wall-mounts or positions on your desktop. Rack-mount hardware is included for optional placement in a 19-inch rack. All ports automatically adjust for straightthrough or crossover cables—you don't have to worry about cable type.

Compatible with existing 10/100 networks and major operating systems, your 5-Port Gigabit Switch from Belkin delivers error-free transfers at maximum network speeds.

#### Benefits

- Adds 5 high-speed, dedicated 10/100/1000 Ethernet ports
- Installs quickly, and offers convenient backward-compatibility
- Auto-senses and adjusts for network speed and cabling type automatically, for easy integration into your existing 10/100 Ethernet network
- Features compact form factor, durable metal chassis, and fan-less design for quiet assimilation into home or small-office environments
- Comes with a Belkin Limited Lifetime Warranty and free technical support

#### Here's what you need



**Manufacturer's  
Lifetime Warranty and  
Free Technical Support**

For additional solutions,  
please visit us at [belkin.com](http://belkin.com)



## Check out our entire line of gigabit solutions



Gigabit Desktop Network PCI Card  
(F5D5005ea)



8-Port Gigabit Switch  
(F5D5141ea8)



16-Port Gigabit Switch  
(F5D5141ea16)



24-Port Gigabit Switch  
(F5D5141ea24)

## Technical Specifications

### Ports

5 RJ45 10/100/1000Mbps ports  
Auto MDI/MDI-X

### Kabeltyp

Category 5e (or better)

### Standards

IEEE 802.3ab  
IEEE 802.3u  
IEEE 802.3  
IEEE 802.3x

### LEDs

Power  
Activity  
Full Duplex  
Half Duplex  
Collision  
10Mbps  
100Mbps  
1000Mbps

### AC Power

Input: 120VAC, 60Hz, 18W  
Output: 12VDC, 1000mA

### Physical Specifications

Size: 6.96 x 4.05 x 1.22 in. (177 x 103 x 31mm)

### Environmental Specifications

	Temperature	Humidity
Operating:	32-104° F (0-40° C)	10-90%
Storage:	-4-158° F (-20-70° C)	10-95%

### Electromagnetic Emissions

FCC Class A, CE Class A, VCCI A

### Safety

UL (UL 60950), CUL, CE, C-Tick

### Warranty

Manufacturer's Lifetime Warranty

### Technical Support

Free Local Technical Support

### Package Includes

5-Port Gigabit Switch  
Power Supply  
Quick Installation Guide  
Warranty Card

### Related Products

F5D5005ea	Gigabit Desktop Network PCI Card
F5D5141ea8	8-Port Gigabit Switch
F5D5141ea16	16-Port Gigabit Switch
F5D5141ea24	24-Port Gigabit Switch

Part Number	Description	UPC
F5D5141ea5	5-Port Gigabit Switch	7-22868-51586-0