

4

3


2

1

THIS DRAWING IS UNPUBLISHED.	RELEASED FOR PUBLICATION - . - .
© COPYRIGHT - By -	ALL RIGHTS RESERVED.

LOC	DIST	REVISIONS					
—	—	P	LTR	DESCRIPTION	DATE	DWN	APVD
			A	REVISED PER ECO-11-022043	07NOV11	KH	PO

1	HALF BOOT SEAL BLACK, 1/4-40 UNS 2-B THREADED NUT	BT1440004	1825619-1
1	FULL BOOT SEAL BLACK, 1/4-40 UNS 2-B THREADED NUT	B1440004	1825612-1
1	5A-125VAC/28VDC; 2A-250VAC, DPST-ON/OFF/ON, LONG BAT TOGGLE, B TERMINALS, SILVER CONTACTS	A203SYCQ04	1825139-9
1	5A-125VAC/28VDC; 2A-250VAC, DPST-ON/ON, LONG BAT TOGGLE, WIRE LUG TERMINALS, SILVER CONTACTS	A201SYZQ04	2-1825138-8
1	0.4VA-20VAC/DC, DPST-ON/ON, LONG BAT TOGGLE, B TERMINALS, GOLD CONTACTS	A201SYCB04	2-1825138-4
1	0.4VA-20VAC/DC, DPST-ON/ON, LONG BAT TOGGLE, WIRE LUG TERMINALS, GOLD CONTACTS	A201SCWZB04	1-1825138-6
1	0.4VA-20VAC/DC, SPST-(ON)/OFF/(ON), SHORT BAT TOGGLE, B TERMINALS RIGHT ANGLE, GOLD CONTACTS	A105MD9AB04	2-1825137-4
1	5A-125VAC/28VDC; 2A-250VAC, SPST-ON/ON, LARGE TOGGLE & BUSHING (15/32), WIRE LUG TERMINALS, SILVER CONTACTS	A101TZQ04	5-1825136-5
1	5A-125VAC/28VDC; 2A-250VAC, SPST-ON/ON, LONG BAT TOGGLE, B TERMINALS, SILVER CONTACTS	A101SYCQ04	4-1825136-5
1	0.4VA-20VAC/DC, SPST-ON/ON, FLATTED TOGGLE, B TERMINALS, GOLD CONTACTS	A101P3CB04	2-1825136-6
1	5A-125VAC/28VDC; 2A-250VAC, SPST-ON/ON, LEVER TOGGLE, B TERMINALS W/VERTICAL SUPPORT, SILVER CONTACTS	A101L1D9V30Q04	1825136-9
1	0.4VA-20VAC/DC, SPST-ON/ON, LONG BAT TOGGLE, B TERMINALS VERTICAL RIGHT ANGLE, GOLD CONTACTS	A101SYAV2B04	1825136-8
1	5A-125VAC/28VDC; 2A-250VAC, SPST-ON/ON, LOCKING TOGGLE, WIRE LUG TERMINALS, SILVER CONTACTS	A101KZQ04	1825136-7
QTY	DESCRIPTION	ALCOSWITCH PART NUMBER	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN KIRAN HOLAL	07NOV2011	 TE Connectivity			
DIMENSIONS: mm 	TOLERANCES UNLESS OTHERWISE SPECIFIED:	CHK OTT, PETER	-	NAME SINGLE AND DOUBLE POLE, SINGLE THROW, PRINTED CIRCUIT BOARD AND WIRE LUG TERMINALS GEMINI SERIES WITH BOOT SEAL KIT			
		APVD OTT, PETER	-				
		PRODUCT SPEC	-				
		APPLICATION SPEC	-	SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
MATERIAL -	FINISH -	WEIGHT -	A300779	C-2110843-9			-
CUSTOMER DRAWING					SCALE 1:1	SHEET 1 OF 1	REV A