

30

26

Universal-Navigation-Kabel/-wire

USB Buchse/ socket

92

schwarz-gummibeschichtet/
black-rubber coated

LED blau/blue

USB2DRIVE
NAVIGATION

AN-MANN®
USB2DRIVE NAVIGATION
INPUT: 12-24V ≈ 1500mA
OUTPUT: 5V ≈ 2x1000mA
≈ 1x2000mA
CE
MADE IN CHINA
iPod, iPhone and Blackberry

Produktionsdatum/
date code

weiße Bedruckung/
white printing

Hohlstecker $\varnothing 1,0 \times \varnothing 3,5 \times 10 \text{ mm}$ /
hollow plug $\varnothing 1,0 \times \varnothing 3,5 \times 10 \text{ mm}$

Flachleitung schwarz 1,5m $\pm 10 \text{ cm}$ lang /
flat cable black 1.5m $\pm 10 \text{ cm}$ long

Hohlstecker $\varnothing 1,4 \times \varnothing 4 \times 10 \text{ mm}$ /
hollow plug $\varnothing 1,4 \times \varnothing 4 \times 10 \text{ mm}$

Hohlsteckerbuchse $\varnothing 1,0 \times \varnothing 3,5 \times 10 \text{ mm}$ /
hollow plug jack $\varnothing 1,0 \times \varnothing 3,5 \times 10 \text{ mm}$

Hohlsteckerbuchse $\varnothing 1,0 \times \varnothing 3,5 \times 10 \text{ mm}$ /
hollow plug jack $\varnothing 1,0 \times \varnothing 3,5 \times 10 \text{ mm}$

18kOhm Widerstand eingebaut zwischen Pin 4 und 5/
18kOhm resistor build-in between pin 4 and 5

Verwendungsbereich/Application range für Anfrage/for inquiry AN5310				Zul. Abweichung/ Allowable deviation		Oberfläche/ Surface		Maßstab/Scale (DIN A3): 1:1		Gewicht/Weight			
								Werkstoff/Work material, Modell-Nr.					
				2010	Datum/Date	Name		Zeichnungsname/Drawing name					
				Erstellt/ Drawn by	22.12.	PK		Carcharger Navigation Universal					
VO	length of hollow plug changed	04.07.11	PK					Zeichnungsnummer/Drawing number		Blatt/ Sheet 1			
VO	dimension of hollow plug changed	16.05.11	PK					Artikelnummer/Part number				5707163	
VO	label printing updated	28.01.11	PK										
VO	---	22.12.10	PK										
Version	Änderung/Change	Datum/Date	Name	Ursprung/Origin Proj. 079/27/10		Ersatz für/Replaced by			Ersatz durch/Replacement through:				