



HRS No.	PART No.	No. OF PIN	A	B	POLARIZING NOSE	
CL610-1041-0	HIF3BA-100-2.54C	1 0	17.25	10.16	1 AT CENTER	
CL610-1051-3	HIF3BA-14D-2.54C	1 4	22.35	15.24		
CL610-1042-2	HIF3BA-16D-2.54C	1 6	24.80	17.78		
CL610-1043-5	HIF3BA-20D-2.54C	2 0	29.95	22.86		
CL610-1044-8	HIF3BA-26D-2.54C	2 6	37.55	30.48		
CL610-1045-0	HIF3BA-30D-2.54C	3 0	42.63	35.56		
CL610-1046-3	HIF3BA-34D-2.54C	3 4	47.75	40.64		
CL610-1047-6	HIF3BA-40D-2.54C	4 0	55.35	48.26		
CL610-1048-9	HIF3BA-50D-2.54C	5 0	68.04	60.96		1 EACH ON LH AND RH SIDES
CL610-1061-7	HIF3BB-50D-2.54C	5 0	68.04	60.96		1 AT CENTER
CL610-1049-1	HIF3BA-60D-2.54C	6 0	80.77	73.66	1 EACH ON LH AND RH SIDES	
CL610-1062-0	HIF3BB-60D-2.54C	6 0	80.77	73.66	1 AT CENTER	
CL610-1064-5	HIF3BA-64D-2.54C	6 4	85.85	78.74	1 EACH ON LH AND RH SIDES	
CL610-1063-2	HIF3BB-64D-2.54C	6 4	85.85	78.74	1 AT CENTER	

NOTE 1) THE NUMBERS OF POLARIZING NOSE DIFFERS AS TO THE NUMBER OF PIN. REFER TO THE FOLLOWING TABLE.  
 2) PRODUCTS OF 50, 60, 64 PINS ARE AVAILABLE IN TWO TYPES. MAKE SELECTION WITH REFERENCE MADE TO NOTE 1).

TO	
PCK	

NO.	MATERIAL	FINISH, REMARKS	NO.	POLYBUTYLENE TEREPHTHALETE	BLACK	UL94V-0
1						

  

CODE NO. (OLD)	FINISH, REMARKS	DRAWN	DESIGNED	CHECKED	APPROVED	RELEASED
		J. MATSUKAWA	J. MATSUKAWA	M. NAKAJIMA	Y. YOSHIMURA	
		92.01.20	92.01.20	92.01.23	92.01.24	

  

DRAWING NO.	PART NO.
ADC3-84167	HIF3 BA - **D - 2.54C
SCALE	CODE NO.
FREE	REFER TO TABLE.
UNITS	
MM	