


ITEM	MOLEX P/N	DESCRIPTION	QTY	UOM
A,B	511631300	2.5 W/B REC HSG	2	PC
C	511641305	2.5 W/B RETAINER	2	PC
D	507528200	Mini-Lock 2.5 W/B Crimp Rec Term 20-22AWG	26	PC
E	884260070	PAPER PRINTED PAPER WHITE (S100X150YAJ)	1	PC

FROM	TO	CABLE DESCRIPTION	COLOR
A1	B13	20 AWG UL1061 BLACK DISCRETE WIRE	BLACK
A2	B12		
A3	B11		
A4	B10		
A5	B9		
A6	B8		
A7	B7		
A8	B6		
A9	B5		
A10	B4		
A11	B3		
A12	B2		
A13	B1		



NOTES

1. Cable assembly to be tested 100% for continuity and polarity.
2. Label text must be 2mm max. In height with Arial font.
3. Connector view shown is from mating side.

P/N:151371303 — MOLEX PN
 MOLEX
 BATCH WK/YR

DETAIL A

PENDING APPROVAL

DATE	REV	DESCRIPTION	REVISED BY
2018.05.29	A	INITIAL RELEASE	SSHIVASHANKA
2018.11.14	B	CABLE SIZE CHANGED FROM 22AWG TO 20AWG	SSHIVASHANKA

SYMBOLS		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION		CURRENT REV DESC:		molex		
▽ = 0	mm	DIMENSION UNITS	SCALE	EC NO: 608031		MINI-LOCK 13 CIRCUIT 300MM		
▽ = 0	NTS	GENERAL TOLERANCES (UNLESS SPECIFIED)		DRWN: SSHIVASHANKA 2018/11/14		PRODUCT CUSTOMER DRAWING		
▽ = 0	ANGULAR TOL ± °			CHK'D:		DOCUMENT NUMBER		
▽ = 0	4 PLACES ±			APPR:		151371303		
▽ = 0	3 PLACES ±			INITIAL REVISION:		DOC TYPE DOC PART REVISION		
▽ = 0	2 PLACES ±			DRWN: SSHIVASHANKA 2018/05/29		PSD 000 B		
▽ = 0	1 PLACE ±			APPR: MNARAYAN01 2018/06/05		MATERIAL NUMBER		
▽ = 0	0 PLACES ±			THIRD ANGLE PROJECTION		15137		
▽ = 0	DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS			DRAWING		CUSTOMER		
▽ = 0				SERIES		GENERAL MARKET		
▽ = 0				SHEET NUMBER		1 OF 1		

DOCUMENT STATUS	RQ	RELEASE DATE