

4

3

2

1

THIS DRAWING IS UNPUBLISHED

RELEASED FOR PUBLICATION

2015

© COPYRIGHT 1995

BY TE CONNECTIVITY

ALL RIGHTS RESERVED.

LOC DIST

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	NC	NEW RELEASE PER E.O. A14887	08DEC1995	CW	RDR
	A	MODIFIED PER E.O. P14945	28DEC1995	CW	RDR
	B	REVISED PER E.O. P17144	27FEB2001	TY	RDR
	B1	REVISED PER EC0-15-001241	26JAN2015	JA	DM

DT 3PIN INTERFACE  
FOR J1939  
USE W3S-J1939 OR  
W3S-J1939-P012 WEDGE LOCK

Dimensions:  
Vertical: .788 [20.01]  
Horizontal: 1.732 [44.00]

Labels: A, B, C

Dimension: 1.890 [48.01]

Labels: DT04-3P-P007, DEUTSCH IPD-USA

DT 3PIN INTERFACE FOR J1939  
USE W3S OR W3S-P012 WEDGE LOCK

DT 3PIN INTERFACE  
FOR J1939  
USE W3S-J1939 OR  
W3S-J1939-P012 WEDGE LOCK

TE INTERNAL PN	DEUTSCH PN
DT04-3P-P007	DT04-3P-P007

3 MATERIAL: RECEPTACLE HOUSING: NYLON 6/6 15% GF,  
COLOR: GREY;  
CONTACTS: COPPER ALLOY, GOLD PLATED.

2. THIS RECEPTACLE MATES WITH THE DT06-3S-XXXX PLUG.  
(XXXX = ALL MODIFICATIONS)  
SEE NOTES FOR APPROPRIATE WEDGE LOCK.

1. CONSULT FACTORY FOR SPECIFICATIONS.

NOTES:

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 17AUG1995 CLARK WOODRUFF	TE Connectivity	
DIMENSIONS: INCHES [mm]		CHK 27FEB2001 ALEX ROLINSKI		
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD 26FEB2001 STEVE BEARD	NAME 3 WAY T-RECEPTACLE -P007 MOD DT SERIES	
0 PLC ± 1 PLC ± 2 PLC ± 3 PLC ±.025 [0.64] 4 PLC ± ANGLES ±0°30'0"		PRODUCT SPEC N/A	SIZE A3	
MATERIAL 3		APPLICATION SPEC N/A	CAGE CODE 4AFU8	DRAWING NO DT04-3P-P007
FINISH N/A		WEIGHT 23.70g	RESTRICTED TO GEN	
		Customer Drawing	SCALE 2:1	SHEET 1 OF 1 REV B1

1470-19 (3/11)