



奇数キャビティ：キャビティ番号及び金型番号  
 偶数キャビティ：トレードマーク  
 ODD CAV:CAVITY & MOLD NO.  
 EVEN CAV:TRADE MARK


奇数キャビティ：トレードマーク  
 偶数キャビティ：キャビティ番号及び金型番号  
 ODD CAV:TRADE MARK  
 EVEN CAV:CAVITY & MOLD NO.



回路番号 1 マーク  
 CKT. NO.1 MARK

回路番号 1  
 CKT. NO.1

回路番号 N  
 CKT. NO.N



**NOTES:**

- 適合ターミナル : 5054311000  
 APPLICABLE TERMINAL : 5054311000
- 嵌合相手 : 505567\*\*\*\*/505568\*\*\*\*  
 MATE WITH : 505567\*\*\*\*/505568\*\*\*\*
- 偶数極に適用。  
 APPLY FOR EVEN CKT.
- アプリケーション仕様書 (コネクタ取扱説明書) : AS-505565-001/-002  
 APPLICATION SPECIFICATIONS (CONNECTOR MANUAL) : AS-505565-001/-002
- 製品仕様書 : 5055650000 PS 000  
 PRODUCT SPECIFICATION : 5055650000 PS 000
- 製品番号 MATERIAL NO.

505565\*\*0\*

極数  
 CIRCUIT SIZE

色  
 COLOR

NO.	COLOR
0	NATURAL
1	BLACK
2	RED
3	YELLOW
4	BLUE
6	GREEN
8	ORANGE

18.75	22.00	5055655160*	16
17.50	20.75	5055655150*	15
16.25	19.50	5055655140*	14
15.00	18.25	5055655130*	13
13.75	17.00	5055655120*	12
12.50	15.75	5055655110*	11
11.25	14.50	5055655100*	10
10.00	13.25	5055655090*	9
8.75	12.00	5055655080*	8
7.50	10.75	5055655070*	7
6.25	9.50	5055655060*	6
5.00	8.25	5055655050*	5
3.75	7.00	5055655040*	4
2.50	5.75	5055655030*	3
1.25	4.50	5055655020*	2
B	A	ポリ袋 POLYBAG PACKAGE オーダー番号 ORDER NO.	極数 CKT. NO.

部品 PART	材質 MATERIAL
ハウジング HOUSING	ポリエステル(PBT), UL94 V-0, 色 : シート2参照 POLYESTER(PBT), UL94 V-0, COLOR : SEE SHEET 2.

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION

REDRAWN EC NO: 121145 DRWN: RWATANABE01 CHK'D: KOMURAKAMI REV APPR: TKANEKO	2017/09/14	GENERAL TOLERANCES (UNLESS SPECIFIED) ANGULAR TOL ± 1.0 ° 4 PLACES ± 0.2 3 PLACES ± 0.2 2 PLACES ± 0.2 1 PLACE ± 0.2 0 PLACES ± 0.2 DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS	DIMENSION UNITS	SCALE
	2017/09/26		mm	5:1
	2017/09/26		DRWN BY	DATE
			RWATANABE01	2017/09/14
		CHK'D BY	DATE	
		KOMURAKAMI	2017/09/26	
		APPR BY	DATE	
		TKANEKO	2017/09/26	
		DRAWING SIZE	THIRD ANGLE PROJECTION	
		A3		

<b>molex</b>			
MICRO-LOCK PLUS 1.25 W/B SINGLE ROW RECEPTACLE HOUSING			
PRODUCT CUSTOMER DRAWING			
SERIES	MATERIAL NUMBER	CUSTOMER	
505565	SEE SHEET2	GENERAL	
DOCUMENT NUMBER	DOC TYPE	DOC PART	SHEET NUMBER
5055650002-SD	PSD	000	1 OF 2

E

D



C

B

A

ORANGE	GREEN	BLUE	YELLOW	RED	BLACK	NATURAL	HOUSING COLOR
5055651608	5055651606	5055651604	5055651603	5055651602	5055651601	5055651600	16
5055651508	5055651506	5055651504	5055651503	5055651502	5055651501	5055651500	15
5055651408	5055651406	5055651404	5055651403	5055651402	5055651401	5055651400	14
5055651308	5055651306	5055651304	5055651303	5055651302	5055651301	5055651300	13
5055651208	5055651206	5055651204	5055651203	5055651202	5055651201	5055651200	12
5055651108	5055651106	5055651104	5055651103	5055651102	5055651101	5055651100	11
5055651008	5055651006	5055651004	5055651003	5055651002	5055651001	5055651000	10
5055650908	5055650906	5055650904	5055650903	5055650902	5055650901	5055650900	9
5055650808	5055650806	5055650804	5055650803	5055650802	5055650801	5055650800	8
5055650708	5055650706	5055650704	5055650703	5055650702	5055650701	5055650700	7
5055650608	5055650606	5055650604	5055650603	5055650602	5055650601	5055650600	6
5055650508	5055650506	5055650504	5055650503	5055650502	5055650501	5055650500	5
5055650408	5055650406	5055650404	5055650403	5055650402	5055650401	5055650400	4
5055650308	5055650306	5055650304	5055650303	5055650302	5055650301	5055650300	3
5055650208	5055650206	5055650204	5055650203	5055650202	5055650201	5055650200	2
ポリ袋 POLYBAG PACKAGE	ポリ袋 POLYBAG PACKAGE	ポリ袋 POLYBAG PACKAGE	ポリ袋 POLYBAG PACKAGE	ポリ袋 POLYBAG PACKAGE	ポリ袋 POLYBAG PACKAGE	ポリ袋 POLYBAG PACKAGE	極数 CKT NO.
オーダー番号 ORDER NO.	オーダー番号 ORDER NO.	オーダー番号 ORDER NO.	オーダー番号 ORDER NO.	オーダー番号 ORDER NO.	オーダー番号 ORDER NO.	オーダー番号 ORDER NO.	

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION

REDRAWN EC NO: 121145 DRWN: RWATANABE01 CHK'D: KOMURAKAMI REV APPR: TKANEKO 2017/09/14 2017/09/26 2017/09/26	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION UNITS	SCALE				
	ANGULAR TOL ± 1.0 °		mm	1:1				
	4 PLACES ± 0.2	DRWN BY: RWATANABE01 DATE: 2017/09/14		MICRO-LOCK PLUS 1.25 W/B SINGLE ROW RECEPTACLE HOUSING				
	3 PLACES ± 0.2	CHK'D BY: KOMURAKAMI DATE: 2017/09/26						
	2 PLACES ± 0.2	APPR BY: TKANEKO DATE: 2017/09/26						
1 PLACE ± 0.2	DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		DRAWING SIZE	THIRD ANGLE PROJECTION	PRODUCT CUSTOMER DRAWING			
0 PLACES ± 0.2			A3		SERIES	MATERIAL NUMBER	CUSTOMER	
					505565	SEE TABLE	GENERAL	
					DOCUMENT NUMBER	DOC TYPE	DOC PART	SHEET NUMBER
					5055650002-SD	PSD	000	2 OF 2