








PART No.	CODE No.	NUMBER OF CONTACTS	A	B	C	D	E	F
DF9B- 9S-1V(32)	CL540-0125-6-32	9	10.1	8.3	6.5	3	4	8.4
DF9B-11S-1V(32)	CL540-0126-9-32	11	11.1	9.3	7.5	4	5	9.4
DF9B-13S-1V(32)	CL540-0127-1-32	13	12.1	10.3	8.5	5	6	10.4
DF9B-15S-1V(32)	CL540-0128-4-32	15	13.1	11.3	9.5	6	7	11.4
DF9B-17S-1V(32)	-	17	14.1	12.3	10.5	7	8	12.4
DF9B-19S-1V(32)	-	19	15.1	13.3	11.5	8	9	13.4
DF9B-21S-1V(32)	CL540-0131-9-32	21	16.1	14.3	12.5	9	10	14.4
DF9B-23S-1V(32)	CL540-0132-1-32	23	17.1	15.3	13.5	10	11	15.4
DF9B-25S-1V(32)	CL540-0133-4-32	25	18.1	16.3	14.5	11	12	16.4
DF9B-31S-1V(32)	CL540-0143-8-32	31	21.1	19.3	17.5	14	15	19.4
DF9B-41S-1V(32)	CL540-0216-0-32	41	26.1	24.3	22.5	19	20	24.4

NOTES 1 : LEAD CO-PLANARITY INCLUDE REINFORCED METAL FITTINGS SHALL BE 0.1mm MAX.
2 HRS MARK AND CAV NO. ARE INDICATED IN APPROX POSITION SHOWN.
3 9 TO 25 CONTACT CONNECTORS HAVE ONE LOCK AT CENTER OF HOUSING.
31 TO 41 CONTACT CONNECTORS HAVE TWO LOCKS AS PER DRAWING.

3	BRASS	SURFACE:TIN PLATED<REFLOW FINISH>1 μ m min UNDER PLATING:COPPER 0.3 μ m min	8	PS	REINFORCEMENT COLLAR
			7	PS	BLACK<PLASTIC REEL>
			6	POLYIMIDE	BROWN<HEAT-RESISTANCE TAPE>
2	PHOSPHOR BRONZE	TIN PLATED<HOT DIP> 1 μ m min	5	POLYESTER	CLEAR<COVER TAPE>
1	POLYAMIDE	BEIGE, UL94V-0	4	PS	CLEAR<EMBOSSED CARRIER TAPE>
NO.	MATERIAL	FINISH , REMARKS	NO.	MATERIAL	FINISH , REMARKS
UNITS mm			SCALE 5 : 1		
COUNT 5 : 1			DESCRIPTION OF REVISIONS DIS-H-006728		
DESIGNED KT. IWAMA			CHECKED AR. TAKAHASHI		
DATE 12. 04. 10			DRAWING NO. EDC3-341297-01		
APPROVED : KH. IKEDA 12. 02. 21			PART NO. DF9B- *S-1V(32)		
CHECKED : AR. TAKAHASHI 12. 02. 21			CODE NO. CL540-		
DESIGNED : SH. HOSODA 12. 02. 21			DRAWN : KR. AJITO 12. 02. 20		
HRS HIROSE ELECTRIC CO., LTD.			1/2		

