







REV	DATE	CHANGE DESCRIPTION
A	2018/11/09	NEW RELEASE PAPER
B	2019/02/18	UPDATE NOTE



MHF4 CONNECTOR



3D VIEW



- NOTES:
- MATERIAL  
FLEX SIZE: 15.4\*6.4mm  
CABLE: Ø1.13mm  
CONNECTOR: OD1.13 RF 1.4H I-PEX MHF4L CONNECTOR (PLUG GOLD PLATED)
  - SOLDER MASK: BLACK.
  - FOR PULL TEST, CAN NOT LIFT UP IN THE VERTICAL DIRECTION.
  - THE CONNECTOR WILL BE PROTECTED WITH A CAP.
  - CONNECTOR MATING RECEPTACLE I-PEX P/N: 20449-001E.

ITEM	MATERIAL NO.	CABLE LENGTH "L2"	CABLE LENGTH "L1"
1	2069941100	93.5mm	100mm

SYMBOLS		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION		CURRENT REV DESC:		molex		
▽ = 0	mm	SCALE	1:1	EC NO: 612233		2.4/5GHZ FLEXIBLE ANTENNA		
▽ = 0	GENERAL TOLERANCES (UNLESS SPECIFIED)		DRWN: KCHENG06		2019/02/18	PRODUCT CUSTOMER DRAWING		
▽ = 0	ANGULAR TOL	±	°	CHK'D: XJSONG	2019/03/14	DOCUMENT NUMBER		
▽ = 0	4 PLACES	±		APPR: XJSONG	2019/03/14	2069941100		DOC TYPE
▽ = 0	3 PLACES	±	0.1	INITIAL REVISION:		PSD	000	REVISION
▽ = 0	2 PLACES	±	0.25	DRWN: KCHENG06	2018/11/09	GENERAL MARKET		B
▽ = 0	1 PLACE	±	0.3	APPR: XJSONG	2018/11/09	SHEET NUMBER		1 OF 1
▽ = 0	0 PLACES	±	0.5	DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		MATERIAL NUMBER		
□ = 0	THIRD ANGLE PROJECTION		DRAWING	SERIES	MATERIAL NUMBER	CUSTOMER		
■ = 0	THIRD ANGLE PROJECTION		A3-SIZE	206994	2069941100	GENERAL MARKET		
▽ = 0	THIRD ANGLE PROJECTION							