

8

7

6

5

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

© COPYRIGHT

ALL RIGHTS RESERVED.

CODINGS ACC. TE INTERFACE DRAWING 208-18037

CODE A

CODE B

CODE C

CODE J

CODE Z

1233538-9

Z

12

MATenet STP CONTACT SPRING

STAINLESS STEEL

Sn

4.83

2

1

2x3-Port MATENET FRAME, CODE Z

PBT GF-10

WATER-BLUE

1

1233538-7

J

12

MATenet STP CONTACT SPRING

STAINLESS STEEL

Sn

4.83

2

1

2x3-Port MATENET FRAME, CODE J

PBT GF-10

BEIGE

1

1233538-3

C

12

MATenet STP CONTACT SPRING

STAINLESS STEEL

Sn

4.83

2

1

2x3-Port MATENET FRAME, CODE C

PBT GF-10

BLUE

1

1233538-2

B

12

MATenet STP CONTACT SPRING

STAINLESS STEEL

Sn

4.83

2

1

2x3-Port MATENET FRAME, CODE B

PBT GF-10

WHITE

1

1233538-1

A

12

MATenet STP CONTACT SPRING

STAINLESS STEEL

Sn

4.83

2

1

2x3-Port MATENET FRAME, CODE A

PBT GF-10

BLACK

1

ASSY PN

CODE

QTY.

DESCRIPTION

MATERIAL

COLOR

WEIGHT [g]

POS

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: mm

MATERIAL see table

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ±0.3

1 PLC ±0.3

2 PLC ±0.2

3 PLC ±

4 PLC ±

ANGLES ±°

FINISH

see table

THIS DRAWING IS A CONTROLLED DOCUMENT.

OWN: HL-EU

CHK: D.ZHU

APVD: F.PAN

PRODUCT SPEC

108-94568

APPLICATION SPEC

116-94431

WEIGHT

CUSTOMER DRAWING

27APR2022

27APR2022

27APR2022

NAME: MATENET 2X3 PORT PLUG

SIZE: A1

CAGE CODE: C=2333538

DRAWING NO: 1

RESTRICTED TO: -

SCALE: 4:1

SHEET: 1 OF 2

REV: B

TE Connectivity

MATENET 2X3 PORT PLUG

1233538-1 CODING A AS SHOWN

MATERIAL MARKING

TE-LOGO

TE-PN OF COMPONET "2x3-PORT MATenet FRAME"

PART REVISION OF COMPONET "2x3-PORT MATenet FRAME"

CONTACT CAVITY NUMBER

DELIVERY: LOOSE PIECES IN BAG IN BOX

DELIVERY CONDITION: RETAINER IN OPEN POSITION

CAVITY FOR MATenet 2Pos. NanoMQS FEMALE INSERT MODULE TE PN 2302450-X

4805 (3/13)

8

7

6

5

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

© COPYRIGHT

ALL RIGHTS RESERVED.

CODINGS ACC. TE INTERFACE DRAWING 208-18037

CODE A

CODE B

CODE C

CODE J

CODE Z

1

2

3

4

5

6

7

8

9

1-2333538-1 CODING A AS SHOWN

MATERIAL MARKING

TE-LOGO

TE-PN OF COMPONET "2x3-PORT MATenet FRAME"

PART REVISION OF COMPONET "2x3-PORT MATenet FRAME"

CONTACT CAVITY NUMBER

DELIVERY: LOOSE PIECES IN BAG IN BOX

DELIVERY CONDITION: RETAINER IN OPEN POSITION

CAVITY FOR MATenet 2Pos. NanoMQS FEMALE INSERT MODULE TE PN 2302450-X

1-2334013-1 A PBT-GF10 1X

TE

6

3

4

5

2

12 11 10 9 8 7

6

9

1-2333538-9	Z	12	MATenet STP CONTACT SPRING	STAINLESS STEEL	Sn	4.83	2
		1	2x3-Port MATENET FRAME, CODE Z	PBT GF-10	WATER-BLUE		1
1-2333538-7	J	12	MATenet STP CONTACT SPRING	STAINLESS STEEL	Sn	4.83	2
		1	2x3-Port MATENET FRAME, CODE J	PBT GF-10	BEIGE		1
1-2333538-3	C	12	MATenet STP CONTACT SPRING	STAINLESS STEEL	Sn	4.83	2
		1	2x3-Port MATENET FRAME, CODE C	PBT GF-10	BLUE		1
1-2333538-2	B	12	MATenet STP CONTACT SPRING	STAINLESS STEEL	Sn	4.83	2
		1	2x3-Port MATENET FRAME, CODE B	PBT GF-10	WHITE		1
1-2333538-1	A	12	MATenet STP CONTACT SPRING	STAINLESS STEEL	Sn	4.83	2
		1	2x3-Port MATENET FRAME, CODE A	PBT GF-10	BLACK		1
ASSY PN	CODE	QTY.	DESCRIPTION	MATERIAL	COLOR	WEIGHT [g]	POS