






P	LTR	DESCRIPTION	DATE	DWN	APVD
	NC	NEW RELEASE PER E.O. PI7240	19APR2001	JA	RDR
	A	REVISED PER E-21-005400	12MAY2021	MR	IG



7. SEE SHEET 2 FOR OTHER KEY ARRANGEMENTS.

6 MATERIAL:
HOUSING: PA66 GF15
GROMMET: VMQ (BURNT RED)

5. THIS PLUG MATES WITH DTM04-12PX-XXXX RECEPTACLE.
(X = A,B,C,D KEYS; XXXX = ALL MODIFICATION)

4 FOR CONTACT AND WIRE PERFORMANCE AND APPLICATION
CHARACTERISTICS SEE ENVELOPE DRAWING 0425-015-0000.


3. SECONDARY WEDGE LOCK SOLD SEPARATELY: WM-12S.

2. DELETED.

1. DELETED.









NOTES: UNLESS OTHERWISE SPECIFIED

CONTACT SIZE	MIN. INSUL. O.D.	MAX. INSUL. O.D.	WIRE RANGE [mm ²] REF ONLY
20	.053 [1.35]	.120 [3.05]	16-22 AWG [1.0-0.5]

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN A. APOSTOL 17APR2001	 TE Connectivity			
DIMENSIONS: INCHES [mm]		CHK D. MEYER 18APR2001				
	TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± 1 PLC ± 2 PLC ± 3 PLC ±.025 [0.64] 4 PLC ± ANGLES ±0°30'0"	APVD R. REED 19APR2001	NAME PLUG 12 CONTACTS, SIZE 20 A,B,C,D KEYS DTM SERIES			
		PRODUCT SPEC 108-151010				
		MATERIAL 	FINISH N/A	APPLICATION SPEC 114-151010	SIZE A3	CAGE CODE 00779
WEIGHT 12 g						
CUSTOMER DRAWING				SCALE 2:1	SHEET 1 OF 2	REV A

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-



DTM06-12SA
KEY -A-
COLOR: GREY

DTM06-12SB
KEY -B-
COLOR: BLACK

DTM06-12SC
KEY -C-
COLOR: GREEN

DTM06-12SD
KEY -D-
COLOR: BROWN

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
INCHES [mm]

MATERIAL

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ±

1 PLC ±

2 PLC ±

3 PLC ±.025 [0.64]

4 PLC ±

ANGLES ±0°30'0"

FINISH

N/A

DWN
A. APOSTOL 17APR2001

CHK
D. MEYER 18APR2001

APVD
R. REED 19APR2001

PRODUCT SPEC
108-151010

APPLICATION SPEC
114-151010

WEIGHT
12 g

CUSTOMER DRAWING

TE Connectivity

NAME
PLUG 12 CONTACTS, SIZE 20
A,B,C,D KEYS
DTM SERIES

SIZE
A3

CAGE CODE
00779

DRAWING NO
C=DTM06-12SX

RESTRICTED TO
-

SCALE
3:2

SHEET
2 OF 2

REV
A

1470-19 (3/13)