

LOOSE PIECE		SPECIFICATIONS						
MATERIAL NUMBER	ENGINEERING NUMBER	STUD SIZE	"S" ±.005 [0.13]	"W" ±.010 [0.25]	"C" MIN.	"L" MAX.	"H"	STOCK ±.001 [0.025] THICKNESS
190540073	B-218-14X	14	.265 [6.73]	.534 [13.56]	.554 [14.07]	1.311 [33.30]	.980 [24.89]	.031 [.79]
190540075	B-218-38X	38	.390 [9.91]					
190540077	B-218-56X	56	.328 [8.33]					
190540080	B-223-04X	4	.119 [3.02]	.250 [6.35]	.209 [5.31]	.835 [21.21]	.980 [24.89]	.031 [.79]
190540081	B-223-06X	6	.146 [3.71]					
190540083	B-223-08X	8	.173 [4.39]					
190540086	B-225-14X	14	.265 [6.73]	.467 [11.86]	.388 [9.86]	1.112 [28.24]	.980 [24.89]	.031 [.79]
190540088	B-225-56X	56	.328 [8.33]					
190540107	B-237-04X	4	.119 [3.02]	.312 [7.92]	.285 [7.24]	.926 [23.52]	.980 [24.89]	.031 [.79]
190540108	B-237-06X	6	.146 [3.71]					
190540110	B-237-08X	8	.173 [4.39]					
190540113	B-237-10X	10	.198 [5.03]					
190540117	B-239-06X	6	.146 [3.71]	.342 [8.69]	.310 [7.87]	.971 [24.66]	---	.031 [.79]
190540118	B-239-08X	8	.173 [4.39]					
190540119	B-239-10X	10	.198 [5.03]					





PARTS ON TAPE

NOTES:

1. MATERIAL:
   (A). RING TONGUE TERMINAL: COPPER
   PLATING: ELECTRO-TIN (.0003 MIN.)
   (B). INSULATION: MOLDED PVC (BLUE)
2. MWID: MAXIMUM WIRE INSULATION DIAMETER
3. WIRE SIZE: 16 -14 AWG
   1.0 -2.5 MM^2
4. ALL DIMENSIONS IN INCHES/[MM].
5. PARTS ARE ROHS COMPLIANT.
6. DIMS. SHOWN ARE FOR REFERENCE ONLY.

DOCUMENT STATUS	P1	RELEASE DATE	2023/10/13 08:25:56

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION

DIMENSION UNITS: INCH/mm | SCALE: NTS

GENERAL TOLERANCES (UNLESS SPECIFIED)

	MM	INCH
4 PLACES	±	±
3 PLACES	±	± 0.005
2 PLACES	± 0.13	± 0.01
1 PLACE	± 0.25	±
0 PLACES	±	±
ANGULAR TOL	± 0.5 °	

DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS

CURRENT REV DESC: REMOVED OBSOLETED PART NUMBERS AS PER PCN#512606.

EC NO: 764691

DRWN:	RAVINR1	2023/08/31
CHK'D:	GGA	2023/10/13
APPR:	GGA	2023/10/13

INITIAL REVISION:

DRWN:	KO	1984/10/25
APPR:	JMACNEIL	2019/07/01

THIRD ANGLE PROJECTION | DRAWING: C-SIZE | SERIES: 19054

molex

RING TONGUE TERMINAL
INSULKRIMP 200-SERIES

PRODUCT CUSTOMER DRAWING

DOCUMENT NUMBER	DOC TYPE	DOC PART	REVISION
190540072	PSD	000	A3

MATERIAL NUMBER	CUSTOMER	SHEET NUMBER
SEE TABLE	GENERAL MARKET	1 OF 1

FORMAT: Eng-lega-master-tb-prod-C
REVISION: E1
DATE: 2021/05/01