




A friend for life

501-359

SCREW EXTRACTORS

All brands of this type of screw extractor, by virtue of their being glass hard, are brittle and liable to snap if improperly used. Once entered into the screw they need to be turned carefully by means of a tap wrench or similar two handed holder. Do not use a spanner or pliers.



SCREW EXTRACTOR

3062 ▲

Manufactured in Germany from chrome vanadium steel with square drive ends. With left hand thread for extracting broken studs and screws. Sold loose.

Order Ref:	No.	Size:	For Screws:	Drill Size:	Weight:	Box Qty:
T3062 15	1	4mm / 5/32"	3 - 6.5mm / 1/8 - 1/4"	2.5mm	4g	6
T3062 18	2	5mm / 3/16"	6.5 - 8mm / 1/4 - 5/16"	3mm	7g	6
T3062 25	3	6.5mm / 1/4"	8 - 11mm / 5/16 - 7/16"	4.5mm	14g	6
T3062 31	4	10mm / 21/64"	11 - 14mm / 7/16 - 9/16"	6mm	25g	6
T3062 43	5	11mm / 7/16"	14 - 19mm / 9/16 - 3/4"	8mm	47g	6
T3062 56	6	15mm / 19/32"	19 - 25mm / 3/4 - 1"	11mm	98g	6
T3062 75	7	20mm / 3/4"	25 - 35mm / 1 - 1 3/8"	14mm	155g	3
T3062 93	8	25mm / 1"	35 - 50mm / 1 3/8 - 2"	21mm	305g	3




SCREW EXTRACTOR SET

3062-1 ▲

5 piece set in plastic box with hinged lid. Display packed. Containing one each of sizes: 1, 2, 3, 4 & 5.

Order Ref:	T3062 01
Weight:	119g
Box Qty:	3




SCREW EXTRACTOR SET

3062-2 ▲

6 piece set in plastic box with hinged lid. Display packed. Containing one each of sizes: 1, 2, 3, 4, 5 & 6.

Order Ref:	T3062 02
Weight:	241g
Box Qty:	3



SCREW EXTRACTOR & TWIST DRILL SET

3061 ▲

10 piece set in hinged strong metal box. Containing one each of: Sizes 1, 2, 3, 4 & 5 and Twist Drills 2.5, 3, 4.5, 6, 8mm. Display packed.

Order Ref:	T3061
Weight:	395g
Box Qty:	1

CALIPERS




VERNIER CALIPER

3447 ▲

Used for internal, external and depth measurements. Locking screw. Bright finish. Metric and imperial graduations. Display packed.

Order Ref:	T3447
Length:	180mm / 7"
Capacity:	118mm / 4 1/2"
Graduation:	0.1mm / 1/128"
Weight:	83g
Box Qty:	3



VERNIER CALIPER

3450 ▲

Used for internal, external and depth measurements. Locking screw. Nickel plated. Metric and imperial graduations. Display packed.

Order Ref:	T3450
Length:	180mm / 7"
Capacity:	118mm / 4 1/2"
Graduation:	0.1mm / 1/128"
Weight:	86g
Box Qty:	3