


6			5		4		3		2		1	
ITEM	PART#	DESCRIPTION	QTY	UOM					FROM	TO	DESCRIPTION	COLOUR
A,B	5023800200	1.25 W/B Single Plg Hsg 2Ckt	2	PC					A1	B1	1X26AWG DISC BK	BLACK
C	5023810000	1.25 W/B Single Plg Term W/Plt	4	PC					A2	B2	1X26AWG DISC BK	BLACK
D	--	WHITE PART ID LABEL	1	PC								



PART NUMBER	TITLE	L1	L2(REF)
2240911022	CLIK-Mate 1.25 R-R 2ckt 150mm disc Sn	150±5	15
2240911023	CLIK-Mate 1.25 R-R 2ckt 300mm disc Sn	300±5	15
2240911024	CLIK-Mate 1.25 R-R 2ckt 600mm disc Sn	600±5	15

MOLEX P/N
MOLEX
BATCH WK/YR

DETAIL A

NOTES

1. CABLE ASSEMBLY TO BE TESTED 100% FOR CONTINUITY AND POLARITY.
2. CONNECTOR VIEW SHOWN IS FROM MATING SIDE.
3.LABEL TEXT MUST BE 2 MM MAX. IN HEIGHT WITH ARIAL FONT.
4.LABEL MUST BE WRAPPED IN FLAG TYPE ON A SINGLE CABLE.

REVISION			
DATE	REV	DESCRIPTION	CHANGER
2023/11/04	C	INITIAL RELEASE	THANUB
RELEASE STATUS	P1	RELEASE DATE	2023/05/05 16:46:44

FUNCTIONAL SYMBOLS	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION	
	DIMENSION UNITS	SCALE
	mm	NTS
	GENERAL TOLERANCES (UNLESS SPECIFIED)	
DIVISIONAL SYMBOLS	ANGULAR TOL	± °
	4 PLACES	±
	3 PLACES	±
	2 PLACES	±
	1 PLACE	±
	0 PLACES	±
	DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS	THIRD ANGLE PROJECTION
		DRAWING
	SERIES	MATERIAL NUMBER
	A4-SIZE	CUSTOMER
	224091	GENERAL MARKET
	SEE TABLE	1 OF 1

CURRENT REV DESC:	
EC NO: 745876	2023/04/11
DRWN: THANUB	2023/05/05
CHK'D: RDOMZALS	2023/05/05
APPR: RDOMZALS	2023/05/05
INITIAL REVISION:	
DRWN: THANUB	2023/01/15
APPR: SKUMAR07	2023/02/06

molex		
SEE TABLE		
PRODUCT CUSTOMER DRAWING		
DOCUMENT NUMBER	DOC TYPE	DOC PART
2240911020	PSD	000
REVISION		C