


















GANG	1	2	3	4	6
<b>BOXES</b>					
(for surface or flush mounting except where stated)  NOTE: All boxes are fitted with an earth terminal	<b>891 ALM</b> <span style="float:right">10</span> Two 20mm knockouts  <b>821 ALM</b> <span style="float:right">10</span> Without knockouts  73 x 73 x 40mm  <b>2140 WHI</b> <span style="float:right">10</span> Surface for Logic only  	<b>891 ALM</b> <span style="float:right">10</span> Two 20mm knockouts  <b>821 ALM</b> <span style="float:right">10</span> Without knockouts  73 x 73 x 40mm  <b>2140 WHI</b> <span style="float:right">10</span> Surface for Logic only  	<b>892 ALM</b> <span style="float:right">5</span> Four 20mm & Four 25mm knockouts  <b>822 ALM</b> <span style="float:right">5</span> Without knockouts  73 x 133 x 40mm  <b>2142 WHI</b> <span style="float:right">5</span> Surface for Logic only  	<b>892 ALM</b> <span style="float:right">5</span> Four 20mm & Four 25mm knockouts  <b>822 ALM</b> <span style="float:right">5</span> Without knockouts  73 x 133 x 40mm  <b>2142 WHI</b> <span style="float:right">5</span> Surface for Logic only  	<b>893 ALM</b> <span style="float:right">5</span> Four 20mm & Four 25mm knockouts  <b>823 ALM</b> <span style="float:right">5</span> Without knockouts  133 x 133 x 40mm  
<b>GRIDS</b>	one <b>3701 ZIC</b> <span style="float:right">10</span> 	one <b>3702 ZIC</b> <span style="float:right">10</span> 	one <b>3734 ZIC</b> <span style="float:right">10</span> 	one <b>3734 ZIC</b> <span style="float:right">10</span> 	two <b>3734 ZIC</b> <span style="float:right">10</span> 
<b>COVER PLATES</b>					
<b>Metalclad</b> Surface <b>Albany</b> ★ Matt Chrome Surface <b>Logic</b> Moulded Flush <b>Albany</b> Matt Chrome <b>Albany</b> Satin Brass <b>Chroma</b> ★ Polished Chrome <b>Grosvenor</b> Brass	<b>3491 ALM</b> <span style="float:right">10</span> 76 x 76mm  <b>3461 MCO</b> <span style="float:right">10</span> 76 x 76mm  <b>3631 WHI</b> <span style="float:right">10</span> 86 x 86mm  <b>3431 MCO</b> <span style="float:right">10</span> 86 x 86mm  <b>3431 SAB</b> <span style="float:right">10</span> 86 x 86mm  <b>3431 PCR</b> <span style="float:right">10</span> 86 x 86mm  <b>4331 POB</b> <span style="float:right">1</span> 86 x 86mm	<b>3492 ALM</b> <span style="float:right">10</span> 76 x 76mm  <b>3462 MCO</b> <span style="float:right">10</span> 76 x 76mm  <b>3632 WHI</b> <span style="float:right">10</span> 86 x 86mm  <b>3432 MCO</b> <span style="float:right">10</span> 86 x 86mm  <b>3432 SAB</b> <span style="float:right">10</span> 86 x 86mm  <b>3432 PCR</b> <span style="float:right">10</span> 86 x 86mm  <b>4332 POB</b> <span style="float:right">1</span> 86 x 86mm	<b>3493 ALM</b> <span style="float:right">5</span> 76 x 137mm  <b>3463 MCO</b> <span style="float:right">5</span> 76 x 137mm  <b>3633 WHI</b> <span style="float:right">10</span> 86 x 146mm  <b>3433 MCO</b> <span style="float:right">5</span> 86 x 146mm  <b>3433 SAB</b> <span style="float:right">5</span> 86 x 146mm  <b>3433 PCR</b> <span style="float:right">5</span> 86 x 146mm  <b>4333 POB</b> <span style="float:right">1</span> 86 x 146mm	<b>3494 ALM</b> <span style="float:right">5</span> 76 x 137mm  <b>3464 MCO</b> <span style="float:right">5</span> 76 x 137mm  <b>3634 WHI</b> <span style="float:right">10</span> 86 x 146mm  <b>3434 MCO</b> <span style="float:right">5</span> 86 x 146mm  <b>3434 SAB</b> <span style="float:right">5</span> 86 x 146mm  <b>3434 PCR</b> <span style="float:right">5</span> 86 x 146mm  <b>4334 POB</b> <span style="float:right">1</span> 86 x 146mm	<b>3496 ALM</b> <span style="float:right">1</span> 137 x 137mm  <b>3466 MCO</b> <span style="float:right">1</span> 137 x 137mm  <b>3636 WHI</b> <span style="float:right">1</span> 146 x 146mm  <b>3436 MCO</b> <span style="float:right">1</span> 146 x 146mm  <b>3436 SAB</b> <span style="float:right">1</span> 146 x 146mm  <b>3436 PCR</b> <span style="float:right">1</span> 146 x 146mm  <b>4346 POB</b> <span style="float:right">1</span> 146 x 146mm

COVER PLATE OPTIONS





866 ZIC <span style="border: 1px solid black; padding: 0 2px;">10</span> 891 ALM <span style="border: 1px solid black; padding: 0 2px;">10</span>	866 ZIC <span style="border: 1px solid black; padding: 0 2px;">10</span> 891 ALM <span style="border: 1px solid black; padding: 0 2px;">10</span>	886 ZIC <span style="border: 1px solid black; padding: 0 2px;">5</span> 892 ALM <span style="border: 1px solid black; padding: 0 2px;">5</span>	886 ZIC <span style="border: 1px solid black; padding: 0 2px;">5</span> 892 ALM <span style="border: 1px solid black; padding: 0 2px;">5</span>	893 ALM <span style="border: 1px solid black; padding: 0 2px;">5</span> 893 ALM <span style="border: 1px solid black; padding: 0 2px;">5</span>	
15001 WHI <span style="border: 1px solid black; padding: 0 2px;">5</span> 86 x 86mm	15002 WHI <span style="border: 1px solid black; padding: 0 2px;">5</span> 86 x 86mm	15003 WHI <span style="border: 1px solid black; padding: 0 2px;">5</span> 86 x 146mm	15004 WHI <span style="border: 1px solid black; padding: 0 2px;">5</span> 86 x 146mm	15006 WHI <span style="border: 1px solid black; padding: 0 2px;">1</span> 146 x 146mm	15008 WHI <span style="border: 1px solid black; padding: 0 2px;">1</span> 146 x 146mm
15101 CHA <span style="border: 1px solid black; padding: 0 2px;">5</span> 86 x 86mm	15102 CHA <span style="border: 1px solid black; padding: 0 2px;">5</span> 86 x 86mm	15103 CHA <span style="border: 1px solid black; padding: 0 2px;">5</span> 86 x 146mm	15104 CHA <span style="border: 1px solid black; padding: 0 2px;">5</span> 86 x 146mm	15106 CHA <span style="border: 1px solid black; padding: 0 2px;">1</span> 146 x 146mm	15108 CHA <span style="border: 1px solid black; padding: 0 2px;">1</span> 146 x 146mm
15101 SCR <span style="border: 1px solid black; padding: 0 2px;">5</span> 86 x 86mm	15102 SCR <span style="border: 1px solid black; padding: 0 2px;">5</span> 86 x 86mm	15103 SCR <span style="border: 1px solid black; padding: 0 2px;">5</span> 86 x 146mm	15104 SCR <span style="border: 1px solid black; padding: 0 2px;">5</span> 86 x 146mm	15106 SCR <span style="border: 1px solid black; padding: 0 2px;">1</span> 146 x 146mm	15108 SCR <span style="border: 1px solid black; padding: 0 2px;">1</span> 146 x 146mm
15101 CHM <span style="border: 1px solid black; padding: 0 2px;">5</span> 86 x 86mm	15102 CHM <span style="border: 1px solid black; padding: 0 2px;">5</span> 86 x 86mm	15103 CHM <span style="border: 1px solid black; padding: 0 2px;">5</span> 86 x 146mm	15104 CHM <span style="border: 1px solid black; padding: 0 2px;">5</span> 86 x 146mm	15106 CHM <span style="border: 1px solid black; padding: 0 2px;">1</span> 146 x 146mm	15108 CHM <span style="border: 1px solid black; padding: 0 2px;">1</span> 146 x 146mm

All Accent Frontplates are supplied with the appropriate grid.

**Dimensions:**  
**1 and 2 Module:** 86 x 86mm  
**3 and 4 Module:** 86 x 146mm  
**6 and 8 Module:** 146 x 146mm  
**Frontplate thickness:** 3.5mm

