




REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
C4		Non CPA and CPA versions on sheet 2 and 3	21MAY2021	VS	CS
C5		TPA LOCKING TYPE ADDED	19OCT2023	JJ	CS
D		See change index D on sheet 4	04SEP2025	OK	SC
D1		REVISION UPDATE	14NOV2025	OK	SC


VERSION TYPE II



MAX Ø14.8
RING GAUGE
Huellkeis



VERSION TYPE I




- ONLY THE GERMAN LANGUAGE SHALL BE BINDING
Massgebend ist der deutsche Text
- DETAILS OF DESIGN ARE LEFT TO TE CONNECTIVITY
Einzelheiten der Ausfuehrung bleiben TE CONNECTIVITY ueberlassen
- PACKAGING: BULK IN PLASTIC BAG IN CARDBOARD BOX
Verpackung: Schuettgut in Kunststoffbeutel in Karton
- TE ORDER NO. 2298721-1 CODING A AS SHOWN
TE-Bestellnummer 2298721-1 Kodierung A wie dargestellt

Retainer and CPA in pre-locking position
Sekundärverriegelung und CPA in Vorraststellung


- MATCHING TO CONTACT TE NO. 2298488 AND 2298510
Passend zu Kontakt TE-Nr. 2298488 und 2298510
- CONFECTION TESTS COMBINED WITH CONTACT LEADS ARE TO BE MADE WITH
RF-ADAPTER 1-523216-0
Konfektionspruefungen in Verbindung mit Leitungen sind durchzufuehren mit
HF-Adapter 1-523216-0

VIEW A




RETAINER IN FINAL LOCKING POSITION
Sekundaersicherung in Endraststellung


CODING VIEW, PLUG SIDE, SIMILARITY AS
Gehaeuse, Steckseite, Darstellung der Kodierungen nur ae hnlich
VIEW 5:1




VIEW 3D EXPLODED
2:1



2298721-9	Z	C	2	RETAINER	PA66-GF	TRAFFIC PURPLE / 4006	1.1	2
			1	HOUSING	PA66-GF	WATER BLUE / 5021		1
2298721-6	F	C	2	RETAINER	PA66-GF	TRAFFIC PURPLE / 4006	1.1	2
			1	HOUSING	PA66-GF	NUT BROWN / 8011		1
2298721-5	E	C	2	RETAINER	PA66-GF	TRAFFIC PURPLE / 4006	1.1	2
			1	HOUSING	PA66-GF	MAY GREEN / 6017		1
2298721-4	D	C	2	RETAINER	PA66-GF	TRAFFIC PURPLE / 4006	1.1	2
			1	HOUSING	PA66-GF	CLARET VIOLET / 4004		1
2298721-3	C	C	2	RETAINER	PA66-GF	TRAFFIC PURPLE / 4006	1.1	2
			1	HOUSING	PA66-GF	LIGHT BLUE / 5012		1
2298721-2	B	C	2	RETAINER	PA66-GF	TRAFFIC PURPLE / 4006	1.1	2
			1	HOUSING	PA66-GF	PURE WHITE / 9010		1
2298721-1	A	C	2	RETAINER	PA66-GF	TRAFFIC PURPLE / 4006	1.1	2
			1	HOUSING	PA66-GF	JET BLACK / 9005		1
TE ORDER NO.	COD.	REV.	QTY.	DESCRIPTION	MATERIAL	COLOUR / SIMILAR RAL	WEIGHT [g]	POS.
THIS DRAWING IS A CONTROLLED DOCUMENT.				DWN G. van de Burch C. Schreutlingen	03OCT2016 17OCT2016	 TE Connectivity		
DIMENSIONS:				TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD W. Mueller			
mm				0 PLC ±0.2 1 PLC ±0.2 2 PLC ±0.2 3 PLC ±0.2 4 PLC ±0.2 ANGLES ±#°	PRODUCT SPEC 108-94709			
				FINISH	APPLICATION SPEC 116-94468			
MATERIAL SEE TABLE siehe Tabelle				WEIGHT -	CAGE CODE -	DRAWING NO C=2298721	RESTRICTED TO -	
CUSTOMER DRAWING				SCALE 5:1	SHEET 1	OF 4	REV D1	



VIEW 3D EXPLODED
2:1



CODING VIEW, PLUG SIDE, SIMILARITY AS
Gehäuse, Steckseite, Darstellung der Kodierungen nur ähnlich
VIEW 5:1







D

C



B

A



REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
-	-	SEE SHEET 1	-	-	-

TE ORDER NO. 2-2298721-1 CODING A AS SHOWN
TE-Bestellnummer 2-2298721-1 Kodierung A wie dargestellt



RETAINER IN FINAL LOCKING POSITION Sekundaersicherung in Endraststellung		CODING VIEW, PLUG SIDE, SIMILARITY AS Gehaeuse, Steckseite, Darstellung der Kodierungen nur ae hnlich VIEW 5:1				
CODING A	CODING B	CODING C	CODING D	CODING E	CODING F	CODING Z

2-2298721-9	Z	D	1	CPA	PA66-GF	RED/3020	1.18	3
			2	RETAINER	PA66-GF	TRAFFIC PURPLE / 4006		2
			1	HOUSING	PA66-GF	WATER BLUE / 5021		1
2-2298721-6	F	D	1	CPA	PA66-GF	RED/3020	1.18	3
			2	RETAINER	PA66-GF	TRAFFIC PURPLE / 4006		2
			1	HOUSING	PA66-GF	NUT BROWN / 8011		1
2-2298721-5	E	D	1	CPA	PA66-GF	RED/3020	1.18	3
			2	RETAINER	PA66-GF	TRAFFIC PURPLE / 4006		2
			1	HOUSING	PA66-GF	MAY GREEN / 6017		1
2-2298721-4	D	D	1	CPA	PA66-GF	RED/3020	1.18	3
			2	RETAINER	PA66-GF	TRAFFIC PURPLE / 4006		2
			1	HOUSING	PA66-GF	CLARET VIOLET / 4004		1
2-2298721-3	C	D	1	CPA	PA66-GF	RED/3020	1.18	3
			2	RETAINER	PA66-GF	TRAFFIC PURPLE / 4006		2
			1	HOUSING	PA66-GF	LIGHT BLUE / 5012		1
2-2298721-2	B	D	1	CPA	PA66-GF	RED/3020	1.18	3
			2	RETAINER	PA66-GF	TRAFFIC PURPLE / 4006		2
			1	HOUSING	PA66-GF	PURE WHITE / 9010		1
2-2298721-1	A	D	1	CPA	PA66-GF	RED/3020	1.18	3
			2	RETAINER	PA66-GF	TRAFFIC PURPLE / 4006		2
			1	HOUSING	PA66-GF	JET BLACK / 9005		1
TE ORDER NO.	COD.	REV.	QTY.	DESCRIPTION	MATERIAL	COLOUR / SIMILAR RAL	WEIGHT [g]	POS.
THIS DRAWING IS A CONTROLLED DOCUMENT.				DWN G. van de Burch 03OCT2016	TE Connectivity			
DIMENSIONS:				CHK C. Schrettlinger 17OCT2016				
TOLERANCES UNLESS OTHERWISE SPECIFIED:				APVD W. Mueller 21OCT2016				
mm				PRODUCT SPEC				
0 PLC ±0.2				108-94709	NAME 4POS,MATE-AX,SOC HSG ASSY,180DEG		RESTRICTED TO	
1 PLC ±0.2				APPLICATION SPEC	SIZE A 1		CAGE CODE	
2 PLC ±0.2				116-94468	DRAWING NO		SHEET 3 OF 4	
3 PLC ±0.2				WEIGHT	C=2298721		REV 01	
4 PLC ±0.2				CUSTOMER DRAWING	SCALE 5:1			
ANGLES FINISH								
MATERIAL SEE TABLE								
siehe Tabelle								

	-	SEE SHEET 1	-	-	-

SING	PA66-GF	BLUE GRAY / 7031		1.03	2
SING	PA66-GF	TRAFFIC PURPLE / 4006		1.03	2
SING	PA66-GF	WATER BLUE / 5021		1.03	1
SING	PA66-GF	TRAFFIC PURPLE / 4006		1.03	2
SING	PA66-GF	NUT BROWN / 8011		1.03	1
SING	PA66-GF	TRAFFIC PURPLE / 4006		1.03	2
SING	PA66-GF	MAY GREEN / 6017		1.03	1
SING	PA66-GF	TRAFFIC PURPLE / 4006		1.03	2
SING	PA66-GF	CLARET VIOLET / 4004		1.03	1
SING	PA66-GF	TRAFFIC PURPLE / 4006		1.03	2
SING	PA66-GF	LIGHT BLUE / 5012		1.03	1
SING	PA66-GF	TRAFFIC PURPLE / 4006		1.03	2
SING	PA66-GF	PURE WHITE / 9010		1.03	1
SING	PA66-GF	TRAFFIC PURPLE / 4006		1.03	2
SING	PA66-GF	JET BLACK / 9005		1.03	1
PTION	MATERIAL	COLOUR / SIMILAR RAL		WEIGHT [g]	POS.
PTION	MATERIAL	COLOUR / SIMILAR RAL		WEIGHT [g]	POS.
ati	04SEPT2025	 TE Connectivity			
ehboune	04SEPT2025				
chrellinger	04SEPT2025				
sPEC	NAME				
-94709	4 POS.MATE-AX.SOC HSG ASSY.180DEG	4 pol.MATE-AX.Buchsengeh Zsb.180Grad _			
CTION SPEC					
-94468	SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO	
-	A1	-	G=2298721	-	
MER DRAWING			SCALE	5:1	SHEET 4 OF 4
				REV D	
