



STACKABLE SNAP-IN HANGERS

Ø1/2" CABLE HANGER



MOLEX P/N	DESCRIPTION
0734300070	1/2" COAXIAL CABLE CONNECTABLE SNAP IN HANGER

Ø7/8" CABLE HANGER



MOLEX P/N	DESCRIPTION
0734300071	7/8" COAXIAL CABLE STACKABLE SNAP IN HANGER

Ø1 1/4" CABLE HANGER



MOLEX P/N	DESCRIPTION
0734300072	1 1/4" COAXIAL CABLE STACKABLE SNAP IN HANGER

Ø1 5/8" CABLE HANGER



MOLEX P/N	DESCRIPTION
0734300073	1 5/8" COAXIAL CABLE STACKABLE SNAP IN HANGER

MATERIAL:
21 GAUGE STAINLESS STEEL 304

PROPERTIES:
CORROSION RESISITANT
OPERATING TEMPERATURE: -40° / +85° C
RoHS COMPLIANT

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION																			
FUNCTIONAL SYMBOLS	DIMENSION UNITS		SCALE		CURRENT REV DESC: NEW DRAWING RELEASE					molex STACKABLE SNAP-IN HANGERS VARIOUS CABLE SIZES									
	-	NTS																	
DIVISIONAL SYMBOLS	GENERAL TOLERANCES (UNLESS SPECIFIED)				PHASE: CO NO: CO-000015068 DRWN: Les Meier 2024-01-03 CHK'D: James Borrelli 2024-09-06 APPR: Les Meier 2024-09-06					PRODUCT CUSTOMER DRAWING									
	MM		INCH							DOCUMENT NUMBER					DOC TYPE	DOC PART	REVISION		
	4 PLACES	±		±						734300070					PSD	000	A		
	3 PLACES	±		±						INITIAL REVISION: DRWN: Les Meier 2024-01-03 APPR: Les Meier 2024-09-06					MATERIAL NUMBER CUSTOMER SHEET NUMBER				
	2 PLACES	±		±															
	1 PLACE	±		±															
	0 PLACES	±		±						DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS					THIRD ANGLE PROJECTION DRAWING SERIES C-SIZE 73430				
ANGULAR TOL ± 0.5°																			
							73430	SEE TABLES		1 OF 1									