


SNAP-IN CABLE HANGER

1/2" COAX CABLE




MOLEX P/N	DESCRIPTION
0734300110	SNAP-IN HANGER FOR 1/2" COAX CABLE

7/8" COAX CABLE



MOLEX P/N	DESCRIPTION
0734300111	SNAP-IN HANGER FOR 7/8" COAX CABLE

1 1/4" COAX CABLE



MOLEX P/N	DESCRIPTION
0734300112	SNAP-IN HANGER FOR 1 1/4" COAX CABLE

1 5/8" COAX CABLE



MOLEX P/N	DESCRIPTION
0734300113	SNAP-IN HANGER FOR 1 5/8" COAX CABLE

2 1/4" COAX CABLE



MOLEX P/N	DESCRIPTION
0734300114	SNAP-IN HANGER FOR 2 1/4" COAX CABLE

MATERIAL:
21 GAUGE STAINLESS STEEL 304

PROPERTIES:
CORROSION RESISTANT
OPERATING TEMPERATURE: -40° / +85° C
RoHS COMPLIANT

FUNCTIONAL SYMBOLS	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION												
= 0 = 0 = 0	DIMENSION UNITS		SCALE		CURRENT REV DESC: NEW DRAWING RELEASE				molex SNAP-IN HANGER VARIOUS SIZE COAXIAL CABLES				
	-		NTS										
	GENERAL TOLERANCES (UNLESS SPECIFIED)												
	DIVISIONAL SYMBOLS			MM	INCH	PHASE: CO NO: CO-000015070 DRWN: Les Meier 2024-05-28 CHK'D: James Borrelli 2024-09-06 APPR: Les Meier 2024-09-06				PRODUCT SALES DRAWING			
4 PLACES		±		±									
3 PLACES		±		±									
2 PLACES		±		±									
1 PLACE		±		±									
0 PLACES		±		±	INITIAL REVISION: DRWN: Les Meier 2024-05-28 APPR: Les Meier 2024-09-06				DOCUMENT NUMBER		DOC TYPE	DOC PART	REVISION
ANGULAR TOL		±	0.5°	734300110					PSD	000	A		
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS				THIRD ANGLE PROJECTION		DRAWING	SERIES	MATERIAL NUMBER		CUSTOMER		SHEET NUMBER	
						C-SIZE	73430	SEE TABLES				1 OF 1	