
HOSE CLAMPS:



MOLEX P/N	DESCRIPTION
0734300170	STAINLESS STEEL HOSE CLAMP 1"-2"
0734300171	STAINLESS STEEL HOSE CLAMP 2"-3"
0734300172	STAINLESS STEEL HOSE CLAMP 2"-10"
0734300173	STAINLESS STEEL HOSE CLAMP 3"-4"
0734300174	STAINLESS STEEL HOSE CLAMP 3"-5"
0734300175	STAINLESS STEEL HOSE CLAMP 5"-6"
0734300176	STAINLESS STEEL HOSE CLAMP 10"-16"

MATERIAL:
STEEL

PROPERTIES:
CORROSION RESISTANT
OPERATING TEMPERATURE: -40° / +85° C
RoHS COMPLIANT

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION

FUNCTIONAL SYMBOLS
FA = 0
FC = 0
FP = 0
DIVISIONAL SYMBOLS

DIMENSION UNITS	SCALE
-	NTS

GENERAL TOLERANCES (UNLESS SPECIFIED)

	MM	INCH
4 PLACES	±	±
3 PLACES	±	±
2 PLACES	±	±
1 PLACE	±	±
0 PLACES	±	±
ANGULAR TOL	± 0.5°	

DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS

CURRENT REV DESC: NEW DRAWING RELEASE

PHASE:
CO NO: CO-000015067
DRWN: Les Meier 2024-06-06
CHK'D: James Borrelli 2024-09-09
APPR: Les Meier 2024-09-09

INITIAL REVISION:
DRWN: Les Meier 2024-06-06
APPR: Les Meier 2024-09-09

molex

HOSE CLAMP, VARIOUS SIZES
WITH VARIOUS HOLE SIZES

PRODUCT CUSTOMER DRAWING

DOCUMENT NUMBER	DOC TYPE	DOC PART	REVISION
734300170	PSD	000	A

THIRD ANGLE PROJECTION	DRAWING	SERIES	MATERIAL NUMBER	CUSTOMER	SHEET NUMBER
	C-SIZE	73430	SEE TABLE		1 OF 1

FORMAT: EngAsgn-TC4b+prod-C
REVISION: A
DATE: 2021/08/11